



Part Number : 2216320001

Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Mid-mount, Surface Mount, Center Height 0mm, 24 Circuits, 0.75µm Gold (Au) Plating, Waterproof IPX7

Series Number : 221632

Status : Active

Product Category : I/O Connectors

Documents & Resources

Drawings

- [Drawing 2216320001_sd.pdf](#)
- [Packaging Design Drawing 2216320001PK-000.pdf](#)

3D Models and Design Files


- [3D Model 2216320001_stp.zip](#)

Specifications

- [Application Specification 2216320001AS-000.pdf](#)
- [Product Specification 2216320001PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	221632
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Mid-mount, Surface Mount, Center Height 0mm, 24 Circuits, 0.75µm Gold (Au) Plating, Waterproof IPX7
Application	Wire-to-Board
Component Type	Receptacle
Product Family	USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles
Product Name	USB 3.2 Gen 2
Type	C
UPC	196823223167

Electrical

Current - Maximum per Contact	0.25A,1.25A,5.0A, See Product Specification
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC/DC

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female

Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Mid-Mount
Net Weight	0.652/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.60mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.750µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	USB Type C Plug/Cable

This document was generated on Apr 07, 2024