

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples




Check Inventory



3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

## Description

This miniature GNSS chip antenna delivers reliable positioning performance in an ultra-compact 3.2 x 1.6 x 0.6 mm SMD package. Featuring a low VSWR of  $\leq 2.0$ , 4.18 dBi peak gain, and 79% total efficiency, it provides robust signal reception for GNSS applications. The PCB edge-mount design enables seamless integration into space-constrained devices for asset tracking, fleet management, and industrial monitoring systems. This RoHS-compliant, MSL Level 1 antenna is engineered for smart grid infrastructure, traffic control, energy systems, and surveillance networks where compact size and dependable GNSS connectivity are essential requirements.



## Features

- Miniature Factor: 3.2 x 1.6 x 0.6 mm
- VSWR:  $\leq 2.0$
- Peak Gain: 4.18 dBi
- Total Efficiency: 79%
- Linear Polarization
- Surface Mount (SMD)
- Integration: PCB Edge Mounting
- [RoHS Compliant](#) | [MSL Level 1](#)

## Applications

- Asset Tracking & Fleet Management
- Traffic Control and Monitoring
- Energy Generation and Storage System
- Data Network Center
- Video Surveillance System
- Smart Grid System

## Ordering Information

Part Number	Description
ACAG0301-1575-T	Ceramic Chip Antenna 1575MHz on Tape & Reel

Note: Other options not listed may be available upon request via [Abracon online support](#)




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples



Check Inventory



3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

## Electrical Specification

Parameter	Specification	Unit
Operating Frequency	1575	MHz
VSWR (Typ.)	< 2.0	:1
Peak Gain	4.18	dBi
Average Gain	-0.56	dBi
Maximum Total Efficiency	79	%
Polarization	Linear	-
Impedance	50	$\Omega$
Radiation Pattern	Omni-directional	-

Note: All measurements were conducted on the evaluation board in free space. Performance will vary depending on the ground plane, application, and environment.

## Mechanical Specification

Parameter	Specification
Antenna Dimension	3.2 x 1.6 x 0.6 mm
Evaluation Board Dimension	90 x 50 mm
Mounting Type	Surface Mount
Mounting Location	PCB Center Mounting
Material(s)	Ceramic
Additional Resources	<a href="#">Download STEP File, Package Drawing, 3D PDF</a>

## Environmental Specification

Parameters	Specifications
Operating Temperature	-40°C ~ +85°C
Storage Temperature	-40°C ~ +85°C
Humidity	55% - 75% R.H.
MSL level	1
RoHS Compliant	Yes




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples




Check Inventory




3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1


## Product Dimensions



TOP VIEW



SIDE VIEW



BOTTOM VIEW

Unit: inches[mm]



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED



# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples




Check Inventory



3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

## Reflection Characteristics –Return Loss



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit: [www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples





Check Inventory




3.2 x 1.6 x 0.6 mm  
**RoHS/RoHS II Compliant**  
 MSL Level = 1

## Radiation Characteristics – 3D & 2D pattern



X-Z Plane



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
 Cave, TX 78738  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
 ISO9001-2015  
 CERTIFIED

# Ceramic Chip Antenna 1575MHz



**ACAG0301-1575-T**

Request Samples




Check Inventory




**3.2 x 1.6 x 0.6 mm**  
**RoHS/RoHS II Compliant**  
**MSL Level = 1**

## X-Y Plane



## Y-Z Plane




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit: [www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
 ISO9001-2015  
 CERTIFIED

# Ceramic Chip Antenna 1575MHz




ACAG0301-1575-T

Request Samples

Check Inventory

3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1



Frequency (MHz)	1565	1575	1585
Avg. Gain (dBi)	-1.26	-0.56	-1.58
Peak Gain (dBi)	3.96	4.18	4.05
Efficiency (%)	73	79	81



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples




Check Inventory



3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1


## Evaluation Board Outline & Matching Circuit

The evaluation board (Abracon ACAG0301-1575-T-EVB) is developed to simplify antenna testing and evaluation. It has an arbitrary size of 90 x 50 mm and includes an SMA connector. The purpose is to give a reference design for an optimal antenna implementation. The evaluation board can also be used to test other implementations by cutting and soldering the PCB into any device.



The evaluation board has a matching circuit implemented next to the antenna. This is aimed at enabling optimization possibilities for the user. The component positions are sized for 0402 (1005 metric) SMD components.

The antenna requires a matching circuit to fine-tune the resonant frequency and achieve optimal balance. The evaluation board is pre-tuned for optimal performance in the 2.4–2.5 GHz range using the components listed below (equivalents may be used):



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee  
Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



ACAG0301-1575-T

Request Samples



Check Inventory



3.2 x 1.6 x 0.6 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

## Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process Classification Temperatures ( $T_c$ )		
Package Thickness	Volume $mm^3$ <350	Volume $mm^3$ $\geq$ 350
<2.5mm	235°C	220°C
$\geq$ 2.5mm	220°C	220°C

Table 2

Pb-Free Process Classification Temperatures ( $T_c$ )			
Package Thickness	Volume $mm^3$ <350	Volume $mm^3$ 350-2000	Volume $mm^3$ >2000
<1.6mm	265°C	265°C	265°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum ( $T_{smin}$ )	100°C	150°C
Temperature maximum ( $T_{smax}$ )	150°C	180°C
Time ( $T_{smin}$ to $T_{smax}$ ) ( $t_s$ )	60 – 120 sec.	60 – 120 sec.
Average ramp-up rate ( $T_{smax}$ to $T_p$ )	3°C/sec. max	3°C/sec. max
Liquidous temperature ( $T_L$ )	183°C	220°C
Time at Liquidous ( $T_L$ )	60 – 150 sec.	30 – 40 sec.
Peak package body temperature ( $T_p$ )*	See Table 1	See Table 2
Time ( $T_p$ )** within 5°C of the specified classification temperature ( $T_c$ )	20 sec.	5 sec.
Ramp-down rate ( $T_p$ to $T_{smax}$ )	6°C/sec. max	3°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

\*Tolerance for peak profile temperature ( $T_p$ ) is defined as a supplier minimum and a user maximum.

\*\*Tolerance for time at peak profile temperature ( $t_p$ ) is defined as a supplier minimum and a user maximum.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit: [www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Ceramic Chip Antenna 1575MHz



**ACAG0301-1575-T**

Request Samples



Check Inventory




**3.2 x 1.6 x 0.6 mm**  
**RoHS/RoHS II Compliant**  
**MSL Level = 1**

## Packaging

Reel (3000 pcs/Reel)

Size of the carton: 404 x 206 x 250 mm

Tape & Reel Dimension



Unit: mm

### Carrier Tape Specifications (mm)

Do	K <sub>0</sub>	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	T	F	P <sub>1</sub>	W	A <sub>0</sub>	B <sub>0</sub>	Reel Qty
1.50 ± 0.1	1.3 ± 0.1	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.10	0.22 ± 0.05	3.5 ± 0.10	4.0 ± 0.1	8.0 ± 0.10	2.0 ± 0.1	3.5 ± 0.1	3,000

### Reel Specifications (mm)

A	W <sub>1</sub>	N	C
178 ± 2.0	8.5 ± 1.0	60	13 ± 0.5

## Additional Resources

STEP File: [ACAG0301-1575-T STEP File](#)

Package Drawing: [ACAG0301-1575-T Package Drawing](#)

3D PDF: [ACAG0301-1575-T 3D PDF](#)

**ATTENTION:** Abracon LLC's products are Commercial-Off-The-Shelf (COTS), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit: [www.abracon.com](http://www.abracon.com)

REVISED: 01-06-26

ABRACON IS  
 ISO9001-2015  
 CERTIFIED