



## Features

- Axial/radial leaded
- Fully compatible with current industry standards
- Weldable nickel terminals
- Low internal resistance
- RoHS compliant*
- Agency recognition: c UL us, TÜV

## Applications

Any application that requires extra protection at elevated ambient temperatures, which the 100 °C trip temperature provides.

- Rechargeable battery pack protection
- Cellular phones
- Laptop computers

# MF-LS Series – PTC Resettable Fuses

## Electrical Characteristics

| Model | $V_{max}$ Volts | $I_{max}$ Amps | $I_{hold}$ | $I_{trip}$ | Initial Resistance | | 1 Hour ($R_1$) Post-Trip Resistance | Max. Time to Trip | | Tripped Power Dissipation | Certifications | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | | | Amperes at 23 °C | | Ohms at 23 °C | | Ohms at 23 °C | Amperes at 23 °C | Seconds at 23 °C | Watts at 23 °C | cUL | TÜV |
| | | | Hold | Trip | $R_{min}$ | $R_{max}$ | $R_{max}$ | | | Typ. | E174545 | R50410733 |
| MF-LS100 | 24 | 100 | 1.0 | 2.5 | 0.070 | 0.130 | 0.260 | 5 | 7.0 | 1.5 | ✓ | ✓ |
| MF-LS180 | 24 | 100 | 1.8 | 3.8 | 0.040 | 0.068 | 0.120 | 9 | 2.9 | 2.0 | ✓ | ✓ |
| MF-LS180L | 24 | 100 | 1.8 | 3.8 | 0.040 | 0.068 | 0.120 | 9 | 2.9 | 2.0 | ✓ | ✓ |
| MF-LS190 | 24 | 100 | 1.9 | 4.2 | 0.030 | 0.057 | 0.100 | 10 | 3.0 | 1.9 | ✓ | ✓ |
| MF-LS260 | 24 | 100 | 2.6 | 5.2 | 0.025 | 0.042 | 0.076 | 13 | 5.0 | 2.3 | ✓ | ✓ |
| MF-LS300 | 24 | 100 | 3.0 | 6.3 | 0.015 | 0.031 | 0.055 | 15 | 4.0 | 2.0 | ✓ | ✓ |
| MF-LS340 | 24 | 100 | 3.4 | 6.8 | 0.016 | 0.027 | 0.050 | 17 | 5.0 | 2.7 | ✓ | ✓ |

## Environmental Characteristics

| Item | Condition | Criteria |
|---|---|---|
| Operating Temperature | -40 °C to +85 °C | |
| Storage Condition | +40 °C max. 70 % R.H. max. | |
| Passive Aging | +70 °C, 1000 hours | ±10 % typical resistance change |
| Humidity Aging | +85 °C, 85 % R.H. 168 hours | ±5 % typical resistance change |
| Vibration | MIL-STD-883C, Method 2007.1 Condition A | $R_{min} \le R \le R1_{max}$ |
| Moisture Sensitivity Level (MSL) | See Note | |
| ESD Classification | Class 6 (per AEC-Q200-2, HBM) | |

## Additional Information

Click these links for more information:

PRODUCT SELECTOR | TECHNICAL LIBRARY | INVENTORY | SAMPLES | CONTACT

## Test Procedures And Requirements For Model MF-LS Series

| Test | Test Conditions | Accept/Reject Criteria |
|---|---|---|
| Visual/Mechanical | Verify dimensions and materials | Per MF physical description |
| Resistance | In still air @ 23 °C | $R_{min} \le R \le R1_{max}$ |
| Time to Trip | At specified current, $V_{max}$, 23 °C, still air | T ≤ max. time to trip (seconds) |
| Hold Current | 30 min. at $I_{hold}$, still air | No trip |
| Trip Cycle Life | $V_{max}$, $I_{max}$, 100 cycles | No arcing or burning |
| Trip Endurance | $V_{max}$, 48 hours | No arcing or burning |

**CALIFORNIA WARNING:** Can expose you to lead, a carcinogen and reproductive toxicant.
See www.P65Warnings.ca.gov

*RoHS Directive 2015/863, Mar 31, 2015 and Annex.

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

## Thermal Derating Chart - $I_{hold}/I_{trip}$ (Amps)


| Model | Ambient Operating Temperature | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|
| | -40 °C | -20 °C | 0 °C | 23 °C | 40 °C | 50 °C | 60 °C | 70 °C | 85 °C |
| MF-LS100 | 1.80 / 3.80 | 1.60 / 3.38 | 1.40 / 2.95 | 1.00 / 2.11 | 0.80 / 1.69 | 0.70 / 1.48 | 0.60 / 1.27 | 0.40 / 0.85 | 0.20 / 0.43 |
| MF-LS180 | 3.10 / 6.54 | 2.60 / 5.49 | 2.20 / 4.64 | 1.80 / 3.80 | 1.30 / 2.74 | 1.10 / 2.32 | 0.90 / 1.90 | 0.60 / 1.27 | 0.30 / 0.64 |
| MF-LS180L | 3.10 / 6.54 | 2.60 / 5.49 | 2.20 / 4.64 | 1.80 / 3.80 | 1.30 / 2.74 | 1.10 / 2.32 | 0.90 / 1.90 | 0.60 / 1.27 | 0.30 / 0.64 |
| MF-LS190 | 3.30 / 7.29 | 2.80 / 6.19 | 2.40 / 5.31 | 1.90 / 4.20 | 1.40 / 3.09 | 1.20 / 2.65 | 1.10 / 2.43 | 0.70 / 1.55 | 0.40 / 0.89 |
| MF-LS260 | 4.30 / 8.60 | 3.70 / 7.40 | 3.10 / 6.20 | 2.60 / 5.20 | 1.90 / 3.80 | 1.60 / 3.20 | 1.40 / 2.80 | 1.10 / 2.20 | 0.60 / 1.20 |
| MF-LS300 | 5.10 / 10.7 | 4.40 / 9.24 | 3.70 / 7.77 | 3.00 / 6.30 | 2.30 / 4.83 | 1.90 / 3.99 | 1.60 / 3.36 | 1.20 / 2.52 | 0.70 / 1.47 |
| MF-LS340 | 5.50 / 11.0 | 4.70 / 9.40 | 4.00 / 8.00 | 3.40 / 6.80 | 2.60 / 5.20 | 2.20 / 4.40 | 1.90 / 3.80 | 1.50 / 3.00 | 0.90 / 1.80 |

## Product Dimensions

| Model | A | | B | | C | | D | | F | |
|---|---|---|---|---|---|---|---|---|---|---|
| | Min. | Max. | Min. | Max. | Min. | Max. | Min. | Max. | Min. | Max. |
| MF-LS100 | 20.9 (0.823) | 23.1 (0.909) | 4.9 (0.193) | 5.2 (0.205) | 0.6 (0.024) | 1.0 (0.039) | 4.1 (0.161) | 5.5 (0.217) | 3.8 (0.150) | 4.2 (0.165) |
| MF-LS180 | 24.0 (0.945) | 26.0 (1.024) | 4.9 (0.193) | 5.2 (0.205) | 0.6 (0.024) | 1.0 (0.039) | 4.1 (0.161) | 5.5 (0.217) | 3.8 (0.150) | 4.2 (0.165) |
| MF-LS180L | 35.0 (1.378) | 37.5 (1.476) | 4.9 (0.193) | 5.6 (0.220) | 0.6 (0.024) | 1.0 (0.039) | 9.6 (0.378) | 11.0 (0.433) | 3.8 (0.150) | 4.2 (0.165) |
| MF-LS190 | 21.3 (0.839) | 23.4 (0.921) | 10.2 (0.402) | 11.0 (0.433) | 0.5 (0.020) | 1.1 (0.043) | 5.0 (0.197) | 7.6 (0.299) | 4.8 (0.189) | 5.4 (0.213) |
| MF-LS260 | 24.0 (0.945) | 26.0 (1.024) | 10.8 (0.425) | 11.9 (0.469) | 0.6 (0.024) | 1.0 (0.039) | 5.0 (0.197) | 7.0 (0.276) | 5.9 (0.232) | 6.1 (0.240) |
| MF-LS300 | 28.4 (1.118) | 31.8 (1.252) | 13.0 (0.512) | 13.5 (0.531) | 0.5 (0.020) | 1.1 (0.043) | 6.3 (0.248) | 8.9 (0.350) | 6.0 (0.236) | 6.6 (0.260) |
| MF-LS340 | 24.0 (0.945) | 26.0 (1.024) | 14.8 (0.583) | 15.9 (0.626) | 0.6 (0.024) | 1.0 (0.039) | 4.8 (0.189) | 6.0 (0.236) | 5.9 (0.232) | 6.1 (0.240 |

NOTE: Longer lead option available. Consult factory.

DIMENSIONS: MM (INCHES)





Terminal material: quarter-hard nickel

### Packaging Specifications

Bulk – 500 pcs. per bag

### Typical Part Marking

Represents total content. Layout may vary.





Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.
The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

## Typical Time to Trip at 23 °C

MF-LS models offer trip temperatures lower than MF-S models for extra protection at elevated temperatures.




## How to Order

**MF - LS 180 L**

Multifuse® Product Designator

Series
LS = Axial Leaded "Strap" Component

Hold Current, $I_{hold}$
100-340 (1.0 Amps - 3.40 Amps)

Lead Option
L = Long Lead Option

BOURNS®

**Americas:** Tel: +1 951-781-5500 • Email: americus@bourns.com
**Mexico:** Tel: +52-614-478-0400 • Email: mexicus@bourns.com
**Asia:** Tel: +886-2-2562-4117 • Email: asiacus@bourns.com
**EMEA:** Tel: +36 88 885 877 • Email: eurocus@bourns.com
**www.bourns.com**

MF-LS, REV. P, 09/26

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.
The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

## Application Notice

- Users are responsible for independent and adequate evaluation of Bourns® Multifuse® Polymer PTC devices in the user's application, including the PPTC device characteristics stated in the applicable data sheet.
- Polymer PTC devices must not be allowed to operate beyond their stated maximum ratings. Operation in excess of such maximum ratings could result in damage to the PTC device and possibly lead to electrical arcing and/or fire. Circuits with inductance may generate a voltage above the rated voltage of the polymer PTC device and should be thoroughly evaluated within the user's application during the PTC selection and qualification process.
- Polymer PTC devices are intended to protect against adverse effects of temporary overcurrent or overtemperature conditions up to rated limits and are not intended to serve as protective devices where overcurrent or overvoltage conditions are expected to be repetitive or prolonged.
- In normal operation, polymer PTC devices experience thermal expansion under fault conditions. Thus, a polymer PTC device must be protected against mechanical stress, and must be given adequate clearance within the user's application to accommodate such thermal expansion. Rigid potting materials or fixed housings or coverings that do not provide adequate clearance should be thoroughly examined and tested by the user, as they may result in the malfunction of polymer PTC devices if the thermal expansion is inhibited.
- Exposure to lubricants, silicon-based oils, solvents, gels, electrolytes, acids, and other related or similar materials may adversely affect the performance of polymer PTC devices.
- Aggressive solvents may adversely affect the performance of polymer PTC devices. Conformal coating, encapsulating, potting, molding, and sealing materials may contain aggressive solvents including but not limited to xylene and toluene, which are known to cause adverse effects on the performance of polymer PTCs. Such aggressive solvents must be thoroughly cured or baked to ensure their complete removal from polymer PTCs to minimize the possible adverse effect on the device.
- Recommended storage conditions should be followed at all times. Such conditions can be found on the applicable data sheet and on the Multifuse® Polymer PTC Moisture/Reflow Sensitivity Classification (MSL) note: https://www.bourns.com/docs/RoHS-MSL/msl_mf.pdf


Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.
The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

# Legal Disclaimer Notice

BOURNS®

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."

- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automotive Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.

- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.

- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for a particular purpose, non-infringement and merchantability.

*For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:*

*Web Page:* https://www.bourns.com/legal/disclaimers-terms-and-policies
*PDF:* https://www.bourns.com/docs/Legal/disclaimer.pdf



Downloaded from Arrow.com.