





STYLE A

STYLE B

INSULATION RESTRICTING

0.10–0.41mm ² [202–810CMA]	100	LOOSE PIECE, BOX	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A				8–326875–1
0.24mm ² [475CMA]	500	LOOSE PIECE	#10	5.00[.197]	0.79–1.40[.031–.055]	24	BLUE	B				2–326875–5
	500	LOOSE PIECE	M3.5[#6]	3.68[.145]	0.79–1.40[.031–.055]	24	BLUE	B				2–326875–4
0.10–0.41mm ² [202–810CMA]	4000	326875 ON TAPE, REEL	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A				 2–326875–1
	500	LOOSE PIECE	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A	 326875			
CIRCULAR MIL AREA	QTY	PACKAGE TYPE	STUD SIZE "D"	DIM "C"	WIRE INSUL. DIA	WIRE SIZE	COLOR CODE	STYLE	BODY	SLEEVE	MATERIAL	PART NO
										FINISH		

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX
	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: 300V MAX
	FOR ORDER ENTRY 1-800-526-5142	CIRCULAR MIL AREA RANGE: SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]			
		0 PLC	± -
		1 PLC	± -
		2 PLC	± -
		3 PLC	± -
		3 PLC	± 0.20[.008]
		4 PLC	± -
MATERIAL		FINISH	
SEE TABLE		SEE TABLE	

DWN	14JAN10
JR RUTH	
CHK	14JAN10
TOM MICHELUTTI	
APVD	14JAN10
MIKE PERCHERKE	
PRODUCT SPEC	
—	
APPLICATION SPEC	
—	
WEIGHT	—
CUSTOMER DRAWING	

TE Connectivity

TERMINAL, NYLON - PIDG - RING TONGUE
WIRE SIZE: 26-22

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A2	00779	C-326875	—		
		SCALE	8:1	SHEET	1 OF 1
				REV	Y1