

## Specification Sheet

Part Number: 157-00226



Special shape provides a .20" lateral adjustment to allow for any misalignment of the stud or incorrect positioning of the tie on the cables.

Easy to install without the need for a tool.

Design provides low insertion and high extraction force.

Stud Mount Lateral Cable Tie, 6.0" Long, Stud Diameter 0.2", 50lbs, PA66HS, Black, 500/pkg

Article Number 157-00226

Type T50SOSWSP5E

Color Black (BK)

Quantity Per pack

Product Description The low profile stud mount allows for several ties to be installed on top of one another. The features can be used to accommodate applications requiring the fastening of a single bundle or multiple bundles on the same stud.

Short Description Stud Mount Lateral Cable Tie, 6.0" Long, Stud Diameter 0.2", 50lbs, PA66HS, Black, 500/pkg

Global Part Name T50SOSWSP5E-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	200
Length L (Imperial)	6.42
Length L (Metric)	163.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.181
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Metric)	1.35

Stud Diameter (Metric)	5.0 mm
Stud Diameter (Imperial)	0.197
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Privacy Policy](#)   [Cookie Policy](#)   [Terms and Conditions](#)