

## Device marker - US-EMSP (75,6X54) - 0828787

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Device marker, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: screw, rivet, lettering field size: 75.6 x 54 mm, Number of individual labels: 2

### Your advantages

- ✓ The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The perforated markers are easy to separate and can be easily fitted
- ✓ Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- ✓ The sheets provide space for including function texts

**RoHS**

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 559683
GTIN	4046356559683
Weight per Piece (excluding packing)	16.000 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	53.7 mm
Width (a)	84.9 mm
Height (c)	0.5 mm
Hole diameter	3.20 mm

## Device marker - US-EMSP (75,6X54) - 0828787

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

Color	white
Components	Silicone-free
Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2
Number of individual labels per row	1
Marking mounting type	screw, rivet

#### Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281103
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

## Device marker - US-EMSP (75,6X54) - 0828787

### Classifications

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

#### Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards