



E176177 H/HM Versions Only

FEATURES

- * 3W Isolated Output
- * 24-Pin DIP Package
- * Efficiency to 82%
- * 2:1 Input Range
- * Regulated Outputs
- * Pi Input Filter
- * Continuous Short Circuit Protection
- * UL60950-1 Approval for H/HM Versions only
- * Safety Meets IEC/EN/UL 62368-1



MODEL NUMBER ⁽¹⁾	INPUT VOLTAGE ⁽²⁾	OUTPUT VOLTAGE	OUTPUT CURRENT	INPUT CURRENT		% EFF. ⁽³⁾	CAPACITOR LOAD MAX.
				NO LOAD	FULL LOAD		
EC3A01□	4.5-6 VDC	5 VDC	600 mA	15 mA	800 mA	75	2200uF
EC3A02□	4.5-6 VDC	12 VDC	250 mA	15 mA	759 mA	79	2200uF
EC3A03□	4.5-6 VDC	15 VDC	200 mA	15 mA	779 mA	77	2200uF
EC3A04□	4.5-6 VDC	±5 VDC	±300 mA	25 mA	779 mA	77	1000uF
EC3A05□	4.5-6 VDC	±12 VDC	±125 mA	25 mA	789 mA	76	1000uF
EC3A06□	4.5-6 VDC	±15 VDC	±100 mA	25 mA	800 mA	75	1000uF
EC3A07□	4.5-6 VDC	3.3 VDC	600 mA	15 mA	582 mA	68	2200uF
EC3A11□	9-18 VDC	5 VDC	600 mA	7.5 mA	325 mA	77	2200uF
EC3A12□	9-18 VDC	12 VDC	250 mA	7.5 mA	313 mA	80	2200uF
EC3A13□	9-18 VDC	15 VDC	200 mA	7.5 mA	316 mA	79	2200uF
EC3A14□	9-18 VDC	±5 VDC	±300 mA	12 mA	325 mA	77	1000uF
EC3A15□	9-18 VDC	±12 VDC	±125 mA	12 mA	325 mA	77	1000uF
EC3A16□	9-18 VDC	±15 VDC	±100 mA	12 mA	316 mA	79	1000uF
EC3A17□	9-18 VDC	3.3 VDC	600 mA	7.5 mA	229 mA	72	2200uF
EC3A21□	18-36 VDC	5 VDC	600 mA	5 mA	158 mA	79	2200uF
EC3A22□	18-36 VDC	12 VDC	250 mA	5 mA	156 mA	80	2200uF
EC3A23□	18-36 VDC	15 VDC	200 mA	5 mA	152 mA	82	2200uF
EC3A24□	18-36 VDC	±5 VDC	±300 mA	7.5 mA	162 mA	77	1000uF
EC3A25□	18-36 VDC	±12 VDC	±125 mA	7.5 mA	158 mA	79	1000uF
EC3A26□	18-36 VDC	±15 VDC	±100 mA	7.5 mA	154 mA	81	1000uF
EC3A27□	18-36 VDC	3.3 VDC	600 mA	5 mA	111 mA	74	2200uF
EC3A31□	36-72 VDC	5 VDC	600 mA	2 mA	78 mA	79	2200uF
EC3A32□	36-72 VDC	12 VDC	250 mA	2 mA	78 mA	80	2200uF
EC3A33□	36-72 VDC	15 VDC	200 mA	2 mA	78 mA	80	2200uF
EC3A34□	36-72 VDC	±5 VDC	±300 mA	3 mA	80 mA	78	1000uF
EC3A35□	36-72 VDC	±12 VDC	±125 mA	3 mA	80 mA	78	1000uF
EC3A36□	36-72 VDC	±15 VDC	±100 mA	3 mA	80 mA	78	1000uF
EC3A37□	36-72 VDC	3.3 VDC	600 mA	3 mA	57 mA	72	2200uF

NOTE:

1. □ Can be None, M, H, HM, MS or HMS.
2. Nominal Input Voltage is 5, 12, 24 or 48VDC.
3. Typical Value at Nominal Input Voltage and Full Load.

章 節	A-4
頁 次	1-1

SPECIFICATIONS

All Specifications Typical at Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	5V	4.5-6V
	12V	9-18V
	24V	18-36V
	48V	36-72V
Input Surge Voltage (100ms max.)	5V	10Vdc max.
	12V	25Vdc max.
	24V	50Vdc max.
	48V	100Vdc max.
Input Filter	Pi Type	

OUTPUT SPECIFICATIONS:

Voltage Accuracy	±2.0% max.	
Voltage Balance (Dual)	±1.0% max.	
Temperature Coefficient	±0.05%/°C max.	
Ripple & Noise, 20MHz BW	3.3V/5V	100mV pk-pk, max.
	12V/15V	1% pk-pk max.
Short Circuit Protection	Continuous	
Line Regulation	Single/Dual (note1)	±0.5% max.
Load Regulation	Single (note2)	±0.5% max.
	Dual (note2)	±1.0% max.


NOTE:

1. Measured from high line to low line.
2. Measured from full load to 10% load.
3. Measured from full load to 1/4 load.
4. Maximum case temperature under any operating condition should not be exceed 95°C (plastic case), 100°C (copper case).


GENERAL SPECIFICATIONS:

Efficiency	See Table	
Isolation Voltage:		
500 VDC min.	Standard Models	
3K VDC min.	(Non-Conductive Black Plastic Only) Suffix "H" Models	
1.5K VDC min.	Suffix "HM" Models	
Isolation Resistance	10 ⁹ Ohm min.	
Switching Frequency	100KHz min.	
Operating Ambient Temperature Range	-25°C to +71°C	
Power De-Rating Curve	See Figure1	
Case Temperature (note4) ... Plastic/Copper case	95°C/100°C max.	
Cooling	Natural Convection	
Storage Temperature Range	-40°C to +100°C	
Humidity	95% RH max. Non Condensing	
MTBF	MIL-HDBK-217F 2000Khrs typ.	
Dimensions ... DIP	1.25×0.80×0.40 inches (31.8×20.3×10.2 mm)	
SMD	1.25×0.80×0.45 inches (31.8×20.3×11.4 mm)	
Case Material:		
Standard Models	Non-Conductive Black Plastic	
Suffix "M" Models	Black Coated Copper with Non-Conductive Base	
Suffix "S" Models	SMD Package	
Weight	12.5g	

Figure1. Typical Derating curve for Natural Convection



Case A Dimensions:



PIN CONNECTION									
500 VDC					1.5K & 3K VDC				
Pin	Single Output		Dual Output		Pin	Single Output		Dual Output	
	DIP	SMD	DIP	SMD		DIP	SMD	DIP	SMD
1,24	+V Input		+V Input		1,24	NP	NC	NP	NC
2,23	NC		-V Output		2,3	-V Input		-V Input	
3,22	NC		Common		4,5	NP	NC	NP	NC
4	NP	NC	NP	NC	9	NC		Common	
5	NP	NC	NP	NC	10,15	NC		NC	
9	NP	NC	NP	NC	11	NC		-V Output	
10,15	-V Output		Common		12,13	NP	NC	NP	NC
11,14	+V Output		+V Output		14	+V Output		+V Output	
12,13	-V Input		-V Input		16	-V Output		Common	
16	NP	NC	NP	NC	20,21	NP	NC	NP	NC
20,21	NP	NC	NP	NC	22,23	+V Input		+V Input	

* NP-NO PIN

* NC-NO CONNECTION WITH PIN

NOTE: Pin Size is 0.02 ± 0.002 Inch (0.5 ± 0.05 mm) DIA
All Dimensions in Inches (mm)
Tolerances Inches: X.XX = ±0.02, X.XXX = ±0.010
Millimeters: X.X = ±0.5, X.XX = ±0.25