Specification Sheet

Part Number: DCT110HIRK2



Provides dual separation between bundles to prevent chafing and abrasion.

150lb. tensile strength ensures enough strength for heavy duty applications.

Straps are releasable for increased serviceability.

Dual Clamp Tie, 19.20" Long, 0.25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 50/pkg

Article Number	115-31100
Type	DCT11
Color	Black (BK)
Quantity Per	pack
Product Description	Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy duty equipment. The unique one-piece design features the dual head centered on the strap.
Short Description	Dual Clamp Tie, 19.20" Long, 0.25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 50/pkg
Global Part Name	DCT11-PA66HIRHSUV-BK

Downloaded from Arrow.com.

Minimum Tensile Strength (Imperial)	150
Minimum Tensile Strength (Metric)	667
Length L (Imperial)	19.2
Length L (Metric)	487.68
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	2.28
Bundle Diameter Max (Metric)	58.0
Thickness T (Imperial)	0.06

Downloaded from Arrow.com.

Thickness T (Metric)	1.4
Height H (Imperial)	0.8
Height H (Metric)	20.32
Mounting Hole Diameter D (Imperial)	0.20 "
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Min (Imperial)	0.20
Mounting Hole Diameter D Max (Imperial)	0.20
Mounting Hole Diameter D Max (Metric)	6.2
Stud Diameter (Metric)	M6
Stud Diamater (Imperial)	1/4

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Downloaded from Arrow.com.

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittant, 1000 hours	+320°F (+160°C)
Operating Temperature intermittant, 5000 hours	+257°F (+125°C)
Operating Temperature intermittant, 500 hours	+329°F (+165°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.