



Part Number : [1202530167](#)
Product Description : Contrinex Inductive Sensor, M12 Housing, 0 - 6mm Operating Distance, Quasi-embeddable, Analog, 0 - 10V Output, 2m 3-wire PUR Cable, 35mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AD-509-M12-320



Documents & Resources

Specifications
[Product Specification 1202530166-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 0 - 6mm Operating Distance, Quasi-embeddable, Analog, 0 - 10V Output, 2m 3-wire PUR Cable, 35mm Housing Length
IP Rating	IP67
Product Family	Contrinex Inductive and Photoelectric Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130063376

Electrical

Polarity	Analog
----------	--------

Physical

Connection	Cable (PUR 2m, 3-wire)
Length	35mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Quasi-embeddable
Operating Distance	0 - 6mm
Output	0-10V
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C