






PRODUCT NUMBER	PITCH
YK604xx0x0J0G	10.00mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 20 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 12Lb-In,
WIRE RANGE: 22 - 12 AWG
1) HOUSING: THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t
3) SCREWS: STEEL, M3.5
APPROVAL: **RA** us

DIMENSION

Dim A	Nx10.0±0.35
Dim B	(N-1)x10.0

N=Number of poles

Poles	Tolerance
2P-4P	±0.20
5P-10P	±0.30
11P-24P	±0.40
25P-30P	±0.50

PART NO.: YK 604XX 0 X 0 J0G

Plated

Code Terminal Screw

0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

No. of poles
02 2 poles
03 3 poles
...
30 30 poles

mat'l. code	surface	tolerance	projection	product family	TERMINAL BLOCK
itr ecn no dr	date	ASME Y14.5 ✓ ASME Y14.5	MM	title	
		tolerances unless otherwise specified		TERMINAL BLOCK	
		angles 0		BARRIER TYPE	
		X±1°		dwg no	YK604xx0x0J0G
		X.XX±0.1		sheet 1 of 1 size	A4
		dr EVAN LU 061414		type	CUSTOMER Drawing
		enrg EVAN LU 061414			
		chr HANKE FENG 061414			
		appd SHI JUN 061414			
sheet revision	A				
index sheet	1				