



Home> Products > MICRO SWITCH™ Toggle Switches> NT> Product Page

62NT1-7-NH



Actual product appearance may vary.

NT Series Toggle Switch, Panel stand - off feature, 2 pole step base, 3 position, Screw terminal, Standard Lever

Features

- Completely sealed switching chamber
- NEMA 3, 3R, 4, and 13
- UL recognized, File E12252, Vol. 1, Section 44
- CSA certified, File LR4442
- CE approved

Potential Applications



- Aerial lifts, scissor lifts, truck mounted tele-handlers, and cranes
- Construction equipment
- Agriculture equipment
- Material-handling equipment
- Factory-floor control units
- Machine tool equipment manufacturers

Description

MICRO SWITCH™ NT Series toggle switches meet the need for a rugged, cost effective toggle switch. Quality construction features include a seal between the toggle lever and bushing, and between the cover and case. These switches can be used where panels are subject to splashes, hosedowns, or outdoor environments. The "Easy-Start" threaded bushing enables quick alignment of mounting nut to decrease the chance of cross threading. The panel stand-off with O -ring feature available on some listings, eliminates the need for behind-the-panel hardware, provides uniform panel height, and provides a panel to cover seal.

Supporting Documentation

-  [Accessory: Lever Sleeve](#)
-  [Terminal Identification](#)
-  [Accessory: Seals](#)
-  [Panel Cutout](#)
-  [Accessory: Nuts](#)
-  [Engineering Drawing](#)

Product Specifications		
Circuitry/Operating action	Keyway Momentary Position  Center Position  Opposite Keyway Momentary Position  6 5 4 ON 6 5 4 OFF 6 5 4 ON	
Product Type	MICRO SWITCH™ Toggle Switch	
Ampere/Voltage Range (Resistive Load)	0.5 A to 18 A at 0.5 Vdc to 28 Vdc,0.5 A at 250 Vdc,0.5 A to 10 A at 0.5 Vac to 277 Vac,0.75 A at 115 Vdc	
Circuitry	DPDT	
Action	3 position	
Mounting	Bushing 15/32 in	
Termination	Screw	
Lever Type	Standard	
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 250, 277 Vac; 3 A - 125 Vac "L"	
Comment	Panel stand - off feature; Thermoplastic case; No hardware	
Availability	Global	
UNSPSC Code	30211908	
UNSPSC Commodity	30211908 Toggle switches	
Series Name	NT	

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search