

# Han-Eco Mod.16-HCC-M40-glanded



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 41 116 0723  |
| Specification      | Han-Eco Mod.16-HCC-M40-glanded  |
| HARTING eCatalogue | <a href="https://harting.com/19411160723">https://harting.com/19411160723</a> |

## Identification

|                             |                             |
|-----------------------------|-----------------------------|
| Category                    | Hoods / Housings            |
| Series of hoods/housings    | Han-Eco® Modular            |
| Type of hood/housing        | Cable to cable housing      |
| Description of hood/housing | With integrated cable gland |

## Version

|                         |                      |
|-------------------------|----------------------|
| Size                    | 16 B                 |
| Module slots            | 5                    |
| Version                 | Top entry            |
| Number of cable entries | 1                    |
| Cable entry             | 1x M40               |
| Locking type            | Double locking lever |

## Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500   |
| Degree of protection acc. to IEC 60529 | IP65   |
| Clamping range                         | 16 ... 28 mm                                   |

## Material properties

|                         |  |
|-------------------------|--|
| Material (hood/housing) | Polyamide (PA)<br>Fibre-glass reinforced |
|-------------------------|--|



**Pushing Performance**  
Since 1945

## Material properties

|  |  |
|--|--|
| Colour (hood/housing)                                      | RAL 9005 (jet black)                     |
| Material (seal)  | NBR                                      |
| Colour (seal)  | RAL 9005 (jet black)                     |
| Material (locking)   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (locking)   | RAL 9005 (jet black)                     |
| Material flammability class acc. to UL 94                  | V-0                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                      |
| RoHS   | compliant                                |
| ELV status   | compliant                                |
| China RoHS   | e  |
| REACH Annex XVII substances                                | Not contained                            |
| REACH ANNEX XIV substances                                 | Not contained                            |
| REACH SVHC substances                                      | Not contained                            |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                     |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)             |

## Specifications and approvals

|                |   |
|----------------|---|
| Specifications | IEC 61984<br>EN 45545-2 Fire protection on railway vehicles |
| UL / CSA       | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076  |
| Approvals      | CE  |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 240 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140131408                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |