



Product: [8050](#) 

Magnet Wire, #20 Sol BC, PUR/NYL Ins

 [Request Sample](#)

Product Description

Magnet Wire, 20AWG (Solid) Bare Copper, PUR/NYL Insulation

Technical Specifications

Product Overview

Suitable Applications:	solderable magnet wire
------------------------	------------------------

Construction Details

Conductor

Size	Stranding	Material
20 AWG	Solid	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PUR/Nylon - Polyurethane + Nylon	0.001 in (0.025 mm)	0.0339 in (0.861 mm)
Overall Cable Diameter (Nominal): 0.034 in (0.86 mm)		

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
10.1 Ohm/1000ft (33.1 Ohm/km)	Single conductor in free air @ 30°C: 1.5 A

Voltage

Breakdown Voltage
2700 V Minimum (at Room Temperature)

Mechanical Characteristics

Bend Radius

Stationary Min.	Installation Min.
0.5 in (13 mm)	0.5 in (13 mm)

Max. Pull Tension:	12.4 lbs (5.62 kg)
Bulk Cable Weight:	3.1 lbs/1000ft (4.6 kg/km)

Standards and Compliance

Sustainability:	CA Prop 65
CEC / C(UL) Compliance:	.
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.610 Revision Date: 07-23-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8050	None	Reel	1 ft	612825194460

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.