





PRODUCT NUMBER
SEE TABLE, SHT 2




spec ref -				dr Chen-Hong Tan		2005/08/18		projection		MM		size A3		scale 3:1	
tolerance std -				eng Terry Luo		2019/04/24						ecn no ELX-DG-33324-1			
ASME Y14.5				chr -		-									
				appr Heaven Cen		2019/04/25		product family AirMax ACCESSORIES				rel level Released			
surface - 		linear		0.X		±0.3		Amphenol FCI		title 7.2MM R/A GUIDE SOCKET 2/3 PAIR		dwg no 10045367		rev E	
				0.XX		±0.10									
				0.XXX		±0.050									
ASME Y14.5		angular		0°		±2°		cat. no. -		Product - Customer Drw				sheet 1 of 2	

PRODUCT NUMBER

10045367-101LF

NOTES:

- ① MATERIAL: ZINC ALLOY.
- ② FINISH: TRIVALENT CHROMATE IRIDESCENT
- ③ APPLICATION SPECIFICATION: GS-20-045.
- ④ REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES.
- 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 6 PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.



spec ref -				dr Chen-Hong Tan		2005/08/18		projection		MM		size A3		scale 1:1	
tolerance std -				eng Terry Luo		2019/04/24						ecn no ELX-DG-33324-1			
ASME Y14.5				chr -		-						rel level Released			
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr Heaven Cen		2019/04/25		product family		AirMax ACCESSORIES					
surface - ASME Y14.5		linear		Amphenol FCI		title 7.2MM R/A GUIDE SOCKET 2/3 PAIR				dwg no 10045367		rev E			
														0.X ±0.3	
														0.XX ±0.10	
		0.XXX ±0.050													
angular		0° ±2°		cat. no. -		Product - Customer Drw				sheet 2 of 2					