


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	PART OBSOLESCENCE	03JUL2024	AR	VG

POS. PER PER	L±0.4	PART-NO.
1	2.54	1
2	5.08	2
3	7.62	3
4	10.16	4
5	12.70	5
6	15.24	6
7	17.78	828296 -7
8	20.32	8
9	22.86	9
10	25.40	1-0
11	27.94	1-1
12	30.48	1-2
13	33.02	1-3
14	35.56	1-4
15	38.10	1-5
16	40.64	1-6
17	43.18	1-7
18	45.72	1-8
19	48.26	1-9
20	50.80	2-0
21	53.34	2-1
22	55.88	2-2
23	58.42	2-3
24	60.96	2-4
25	63.50	2-5
26	66.04	2-6
27	68.58	2-7
28	71.12	2-8
29	73.66	2-9
30	76.20	3-0
31	78.74	3-1
32	81.28	3-2
33	83.82	3-3
34	86.36	3-4
35	88.90	3-5
36	91.44	3-6
37	93.98	3-7
38	96.52	3-8
39	99.06	3-9
40	101.60	4-0
41	104.14	4-1
42	106.68	4-2
43	109.22	4-3
44	111.76	4-4
45	114.30	4-5
46	116.84	4-6
47	119.38	4-7
48	121.92	4-8
49	124.46	4-9
50	127.00	5-0



- ① MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: MIN. 2.5µm TIN OVER Min 1.27µm NICKEL
- ② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ③ OBSOLETE

①	CONTACT PIN	CuZn	2
COLOUR:GREEN	PIN HOUSING	PBT	1
FINISH/COLOR	PART DESCRIPTION	MATERIAL	ITEM NO.


DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±0.2

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -



DWN G.Holous 17AUG1989

CHK M.Schaarschmidt -

APVD -

PRODUCT SPEC 108-18012

APPLICATION SPEC -

WEIGHT -

MATERIAL

SEE TABLE

FINISH

SEE TABLE



TE Connectivity

NAME

SPEZ. AMPMODU II STIFTELEISTE
ZWEIREIHIG

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-828296

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV D2