



Part Number : [1716920204](#)

Product Description : Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 4 Circuit, UL 94V-0, Glow-Wire Capable, Black

Series Number : 171692

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[1716920204_sd.pdf](#)

[1716920200-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[768232000-AS-000.pdf](#)

[1054171000-PS-000.pdf](#)

[1054171000-PS-CH-000.pdf](#)

[1054171000-PS-KO-000.pdf](#)


[1054171000-PS-SPA-000.pdf](#)

[1720631000-PS-000.pdf](#)

[1720631000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

	61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	171692
Description	Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 4 Circuit, UL 94V-0, Glow-Wire Capable, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Mega-Fit
UPC	191130070596

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.640/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mega-Fit Right-Angle, Dual Row, Through Hole Headers	<u>172064</u>
Mega-Fit Vertical, Dual Row Through Hole Headers	<u>172065</u>
Mega-Fit Right-Angle Dual Row Headers	<u>76825</u>
Mega-Fit and Mega-Fit Slim Vertical Dual Row Headers	<u>76829</u>
Mega-Fit Free Hanging Dual Row Plug Housings	<u>105411</u>

Use with Part(s)

Description	Part Number
Mega-Fit Tangless TPA-Capable	<u>768230345</u>

Crimp Terminal, Female, Tin (Sn) Plating, 10 AWG, Reel	
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 16+16 or Single 12 AWG, Reel	<u>768230343</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>768230344</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 10 AWG, Reel	<u>1720630335</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	<u>1720630333</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>1720630334</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 10 AWG, Reel	<u>1720631335</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	<u>1720631333</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>1720631334</u>
Mega-Fit Terminal Position Assurance (TPA) Retainer, 2 Circuits, 5.70mm Pitch, UL 94V-0, Glow-Wire Capable, Natural	<u>1054150002</u>

This document was generated on May 14, 2026