


Part Number : [639023900](#)

Product Description : FineAdjust Applicator for Insulation OD 1.40-1.70mm - 24-18 AWG

Series Number : 207127

Status : Active

Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

[ATS-639023900-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638004900-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Insulation OD 1.40-1.70mm - 24-18 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982652675
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	4685.046/g
------------	------------

Mates With / Use With

Use with Part(s)

Description	Part Number
TM-2000 Universal Press	638008300
TM-2000 Universal Press (Europe 220V)	638008400
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	638017200
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	638017300
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	638017600
Use With	Most Industry Standard Presses or Wire Process Machines

Applicable Parts

Description	Part Number
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, Double 22+22 or Single 24-18 AWG, Reel	39000038
Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, Double 22+22 or Single 24-18 AWG, Reel	39000040
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, Double 22+22 or Single 24-18 AWG, Reel	39000059
Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze,	39000061

Double 22+22 or Single 24-18 AWG, Reel	
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	<u>39000073</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 24-18 AWG, Reel	<u>39000075</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 24-18 AWG, Reel	<u>39000120</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 24-18 AWG, Bag	<u>39000121</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 24-18 AWG, Reel	<u>39000126</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 24-18 AWG, Reel	<u>39000181</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	<u>39000207</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 24-18 AWG, Reel	<u>39000213</u>
Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 24-18 AWG, Reel	<u>39000219</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	<u>39000428</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 24-18 AWG, Reel	<u>39000430</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	<u>40130851</u>
Mini-Fit Jr. Crimp Grounding	<u>304901002</u>

Terminal, 24-18 AWG, Reel, Phosphor Bronze, Tin or Select Gold (Au)	
Mini-Fit Jr. Crimp Grounding Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 24-18 AWG, Reel	<u>304902002</u>
Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)	<u>444761111</u>
Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)	<u>444781111</u>
Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, Gold (Au) Selective	<u>444781211</u>
Mini-Fit Jr. Plus Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, Select Gold (Au)	<u>444851211</u>
Mini-Fit Plus Female Crimp Terminal, 20-18 AWG, Copper Alloy, Tin (Sn) Plating, Reel	<u>457501111</u>
Mini-Fit Plus Female Crimp Terminal, 20-18 AWG, Copper Alloy, 0.76µm Gold (Au) Selective Plating, Reel	<u>457501211</u>
Mini-Fit Plus Crimp Terminal, 20-18 AWG, Reel, Tin (Sn) Plating	<u>460121141</u>
Mini-Fit Plus Crimp Terminal, 20-18 AWG, Reel, 0.76µm Selective Gold (Au) Plating	<u>460121241</u>
Mini-Fit Plus High Mating Cycle Female Crimp Terminal, 20-18 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area	<u>460181541</u>
Mini-Fit HCS Crimp Terminal, 20-18 AWG, Reel, Copper (Cu) Alloy, .76µm Tin (Sn)	<u>444761211</u>