
281792-3 Product Details

Live Product Chat



281792-3

TE Part Number: 281792-3

Active

Add to Part List

.100 AMPMODU Headers, Housings & Contacts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Housing
- Preloaded
- Number of Positions = 6
- Housing Type = Receptacle
- Contact Type = Receptacle

View all Features | Find Similar Products

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples NEW!

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Housing
- Number of Positions = 6
- Mating Connector Lock = Without
- Mating Polarization = Without
- Wire Insulation Diameter (mm [in]) = 1.00 [0.039]
- Keyed = No
- Connector Series = HE13 / HE14
- Wire Termination Type = Crimp, Insulation Displacement Crimp (IDC)

Mechanical Attachment:
- Preloaded = Yes

Body Related Features:
- Housing Type = Receptacle
- Number of Rows = Dual
- Centerline, Matrix (mm [in]) = 2.54 [.100]
- Wire Range (mm [AWG]) = 0.08-0.15² [28-26]

Contact Related Features:
- Contact Type = Receptacle
- Contact Mating Area Plating Material = Tin
- Contact Material = Phosphor Bronze

Housing Related Features:
- Housing Color = Blue
- Housing Flammability Rating = UL 94V-0
- Housing Material = PBT - GF

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Terminate To = Wire

Packaging Related Features:
- Packaging Method = Loose Piece

Other:
- Brand = AMP

© 2008 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.