



TE Internal #: 2340165-1

Board-to-Board Card Edge Power Connector, 92 Position, 5.08 mm  
[.2 in] Centerline, Power & Signal, 8 Power Positions, 84 Signal  
Positions

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Card Edge Power Connectors



Connector System: **Board-to-Board**

Number of Positions: **92**

Centerline (Pitch): **5.08 mm [ .2 in ]**

Contact Current Rating (Max): **31 A**

Circuit Application: **Power & Signal**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Card Edge Type	HD+

Configuration Features

Number of Positions	92
Number of Power Positions	8
Number of Signal Positions	84
Number of Dual Positions	46

Electrical Characteristics

Operating Voltage	100 V
-------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Current Rating (Max)	31 A
Contact Mating Area Plating Material	Gold (Au)



Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	5.08 mm [.2 in]
--------------------	-----------------

Dimensions

Power Contact Centerline	5.08 mm [.2 in]
--------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2343428-1  
HD+ CE, RA, CRPS

Customers Also Bought

TE Part #284052-E  
SRCA 2,54 3 M 1 SMD 137 E1 094 \*  
GURT \*

TE Part #581851-000  
55A6262-26-9/96-9CS2275

TE Part #3206430001  
HT-SCE-3/16-2.0-9

TE Part #5-826936-0  
AMP AMPMODU II PIN HDR.

TE Part #2318579-2  
RCPT CONN R/A SMT 76 POSN QSFP-DD WSHRS

TE Part #2342933-3  
QSFP-DD 1X1, STANDARD, W/ EXTRUDED HS

TE Part #2358256-1  
SBCE, 2X25P

TE Part #1-100103-0  
10P.A/L.STRAIN REL.

Documents

2X4P-2X42S, STRADDLE, HD+ CE

English

Customer View Model

ENG\_CVM\_CVM\_2340165-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2340165-1\_A.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_2340165-1\_A.3d\_igs.zip

English



3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Application Specification

English

Agency Approvals

UL Report

English