




LPDDR4

K4FBE3D4HM-GFCL



OVERVIEW

SPECIFICATIONS

RELATED RESOURCES

RELATED INSIGHTS

Versatile LPDRAM for mobile solutions

Samsung’s groundbreaking LPDDR4 transfers data faster with less energy, multiplying design options for ultra-thin devices, AI, VR and wearables.

Specifications

Density	32 Gb	Org.	x32
Speed	4266 Mbps	Voltage	1.8 / 1.1 / 1.1 V
Temp.	-40 ~ 95 °C	Package	200FBGA
Product Status	Mass Production		

SEE ALL


Related insights



Samsung Begins Mass Production of Industry’s First 12Gb LPDDR5

Based on the latest mobile DRAM standard, the new Samsung 12Gb LPDDR5 maximizes the potential of 5G and AI features in future flagships.

[LEARN MORE >](#)



Samsung Launches Highest-capacity Mobile DRAM to

New 12GB LPDDR4X joins 512GB eUFS to enable a seamless user experience in smartphones with multi-cameras, 2X screen sizes, and AI and 5G features

[LEARN MORE >](#)



All product specifications reflect internal test results and are subject to variations by user’s system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Insights

[Product finder](#)

[Technical resources](#)

[TCO calculator](#)

[About us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

[IMAGE SENSOR](#)

[SECURITY SOLUTIONS](#)

[DISPLAY IC](#)

[POWER IC](#)

SOLUTIONS

[APPLICATIONS](#)

Other Sites

[中文\(简体\)](#)

[Samsung Business](#)

[Memory \(日本語\)](#)

[Exynos](#)

[LED](#)

[Display](#)

[Worker Safety](#)

Follow us



Copyright © 1995-2019 SAMSUNG All Rights Reserved.

[PRIVACY](#) [LEGAL](#) [SITEMAP](#)

This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.