


SKINDICHT® SVRE/SVRE-M

Nickel-plated brass cable clamp with PG & metric thread



Complete the installation



SKINDICHT®
SM locknuts
page 542



SKINDICHT®
O-rings
page 555

The SKINDICHT® SVRE cable clamp is a compact general-purpose cable clamp with an adjustable multi-layered bushing which accommodates a large cable diameter range.

Application advantage

- Provides cost savings: storage of fewer sizes due to adjustable bushing
- Suitable for a wide variety of applications that require compact, reliable strain relief
- Cost-effective strain relief solution

Approvals



Technical data



Material:

- body: nickel-plated brass
- bushing/incised sealing: CR
- PG: CR
- metric: NBR



O-rings:

add O-rings, page 555



Temperature range:

-20°C to +80°C



IP Protection:

IP54



Locknuts:

add SKINDICHT® SM, page 542

Part number	Outer thread	Inner thread	Incised sealing ring (oF)	Max. internal diameter	Wrenching flats		Overall length (C)	Thread length (D)	Pack size
			in	in	(SW1) in	(SW2) in	in	in	
PG									
52005540	PG 9	PG 9	0.20 / 0.31	—	0.67	0.59	0.890	0.236	100
52000310	PG 11	PG 11	0.28 / 0.39 / 0.49	—	0.79	0.71	0.890	0.236	50
52000320	PG 13	PG 13	0.28 / 0.41 / 0.51 / 0.63	—	0.87	0.79	1.028	0.256	50
52000330	PG 16	PG 16	0.31 / 0.41 / 0.51 / 0.63	—	0.94	0.87	1.067	0.256	50
52000340	PG 21	PG 21	0.43 / 0.59 / 0.71 / 0.79	—	1.18	1.10	1.166	0.276	50
52000350	PG 29	PG 29	0.75 / 0.91 / 1.06 / 1.22	—	1.57	1.46	1.284	0.315	50
52000360	PG 36	PG 36	0.98 / 1.10 / 1.22 / 1.38	—	1.97	1.85	1.520	0.354	20
52005550	PG 42	PG 42	1.38 / 1.54 / 1.67 / 1.81	—	2.24	2.13	1.717	0.394	10
52005560	PG 48	PG 48	1.59 / 1.73 / 1.85 / 1.99	—	2.52	2.36	1.776	0.394	10
Metric									
52104980	M16 x 1.5	PG 9	0.20 / 0.31	0.47	0.71	0.59	0.851	0.197	100
52104990	M20 x 1.5	PG 11	0.28 / 0.39 / 0.49	0.59	0.87	0.71	0.890	0.236	50
52105000	M20 x 1.5	PG 13	0.28 / 0.41 / 0.51 / 0.63	0.59	0.87	0.79	1.008	0.236	50
52105010	M20 x 1.5	PG 16	0.31 / 0.41 / 0.51 / 0.63	0.59	0.94	0.87	1.048	0.236	50
52105002	M25 x 1.5	PG 21	0.43 / 0.59 / 0.71 / 0.79	0.79	1.18	1.10	0.921	0.276	50
52105003	M32 x 1.5	PG 29	0.75 / 0.91 / 1.06 / 1.22	1.06	1.57	1.46	1.284	0.315	50
52105004	M40 x 1.5	PG 36	0.98 / 1.10 / 1.22 / 1.38	1.34	1.97	1.85	1.481	0.315	20
52105005	M50 x 1.5	PG 42	1.38 / 1.54 / 1.67 / 1.81	1.73	2.24	2.13	1.678	0.354	5
52105006	M63 x 1.5	PG 48	1.59 / 1.73 / 1.85 / 1.99	2.13	2.60	2.36	1.776	0.394	5