

MICRO SWITCH


FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW825551-D6

APZ4260




NOTES

- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 3 1/2 OZ MAX

RELEASE FORCE — — — 3/4 OZ MIN

DIFFERENTIAL TRAVEL — — .004 — .040


OVERTRAVEL — — — .156 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L96 15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

L288
L315
L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.8/.03
ONE PLACE	X,X	0.4/.016	X,X	0.38/.015
TWO PLACES	X,X,X	0.15/.006	X,X,X	0.13/.005
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

SI METRIC

DESIGN UNITS

US CUSTOMARY

WEIGHT .079 LB

BZ-2RW825551-D6

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-11683

DRAWING NUMBER

7

ISSUE

CHECK

REVISIONS

A C067209

J A P

MAY 90

B CO-

75204B

JWB

1 FEB 94

C C080938

DLT

7 JUN 95

D C093346

DLT

17 SEP 98

E 200763

C S L

10 JUL 00

F 0017579

KRB

08DEC05

CHECK

11 NOV 94

11 NOV 94

11 NOV 94

11 NOV 94

11 NOV 94

11 NOV 94

FORMTEK

FO-52848-A

DRAWN

NOV 82

NOV 82