

Features

RoHS complicant
Usage in home appliance, fan heater, fireplace, etc
Cut power and stop control system when the setting time to be ended
Nicely precise construction super low noise
Time setting range: 15,30,60,120,180minutes
Rated voltage and current: AC 250V/2.5A ; AC 125V/5A
Operating Direction: CW
Working Direction: CCW
Working Angle:270± 5°
Operating Temperature: -10°C ~ +60°C
Timing Tolerance: ±10% MAX
Insulation Resistance: 100MΩ
Insulated Electricity Power: 1500 VAC/ 1Min
Operating Torque: 1.0 ~ 5.0 kg-cm
Release Torque: 0.5 ~ 4.0 kg-cm
Endurable Life: 10,000 times and above
For any technical support or suggestion, please kindly go to our [forum](#).

Technical Details

Dimensions80mm x 70mm x 31mm
Weight G.W 52g
Battery Exclude

ECCN/HTS

ECCN ERA99
HSCODE9106900000

Questions and Answers

Have a question about this? Ask people who



Mechanical Timer

SKU 311990000     

IN STOCK
44 Available

ADD TO CART

- Description
- Technical Details
- Questions and Answers

✖
Notify me when it's back in stock

SUBMIT
^

POPULAR SEARCHES

PCB Manufacturing PCB Assembly PCB Layout 3D Printing PCB Stencil Lora ReSpeaker Grove Lidar GPS Can-Bus Arduino Arduino Shield Beaglebone
Raspberry Pi FPGA LinkIt ONE Crazyflie 2.0 Raspberry Pi 3 Model B RF Explorer DSO Nano v3 HiKey rplidar raspberry pi relay RPLIDAR A2

Company

About Seeed
Distributors
Careers
Contacts

Help Center

How to Get Help
FAQ
Technical Support
Shipping & Order
Warranty & Returns
Payment Information

Community

Project Hub
Forum
Blog
Wiki


Stay Tuned

Subscribe to our newsletter.



Select Language

▼

Select Language

▼