

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/09	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 7 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 12
A = .156 [3.96] x No. of Positions
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				TITLE .156 [3.96] POWER HEADER STRAIGHT, WITH REAR LOCK			
Holes				SIZE			
.X ± .10				PART NO.			
.XX ± .020				LHC-XX-TS			
.XXX ± .015				REV.			
.XXX ± .010				SCALE: NTS			
APPROVALS				SHEET 1 OF 1			
DATE							
DRAWN							
SS							
CHECKED							
APPROVED							

6

5

4

3

2

1