




NOTES:

1. 100% ELECTRICAL TEST FOR CONTINUITY, OPENS AND SHORTS.
2. THE MATED BUS-BAR SHOULD HAVE SURFACE ROUGHNESS Ra 1.6um MAX. SHOULD HAVE PLATING 3um MIN. SILVER IN CONTACT AREA, AND 1.27um MIN. Ni OVERALL.
3. SILVER PLATING CONTACT MAY DISCOLOR IN AIR, BUT NO PERFORMANCE ISSUE
4. LOW HALOGEN REQUEST: Br<900ppm, Cl<900ppm, Br+Cl<1500ppm PER HOMOGENEOUS MATERIAL
5. LABEL CONTENT AS SHOWN

XXXXXXX-X
MADE IN CHINA
TE YYWW

TE P/N
YY: YEAR;WW: WEEK

6. WIRE ALLOWABLE CURRENT: 75A FOR 6AWG
7. OPERATING TEMPERATURE: -20C~80C
8. FLAMMABILITY: CONNECTOR MEET UL 94V-0, WIRE MEET VW-1
9. THE CABLE ASSEMBLY SHOULD BE UL AND RoHS2(2011/65/EU) COMPLIANT.
10. M3 NUT WITHSTAND 44N min. PUSH OUT FORCE IN HOUSING.

WIRING CHART		
FROM	TO	WIRE
J1-P1	J3	BLACK
J1-P2	J2	RED

2337275-2	100±10	NA
2337275-1	250±10	NA
TE P/N	L	CUSTOMER P/N,REV.

1	PC	RA CCJ CONNECTOR TE 2326688-1	8
1	PC	LABEL	7
2	PC	M3 NUT	6
AR	MR	HEAT SHRINK TUBE, BLACK	5
AR	MR	UL WIRE 6AWG RED	4
AR	MR	UL WIRE 6AWG BLACK	3
AR	MR	HEAT SHRINK TUBE, BLACK	2
2	PC	R-TERMINAL 6AWG M8	1
-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ADAM CHEN CHK - APVD DAVID ZHANG PRODUCT SPEC 108-152035 APPLICATION SPEC 114-152042 WEIGHT 0 CUSTOMER DRAWING	24MAY2018 - 24MAY2018	TE Connectivity		NAME Cable AssY, RA CCJ TO R TERMINAL		SIZE A2	CAGE CODE 00779	DRAWING NO C=2337275	RESTRICTED TO -
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		SCALE N.T.S		SHEET 1 of 2		REV A			

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY ENVIRONMENTAL STANDARD TEC-138-702

Downloaded from [Arrow.com](https://arrow.com).