



Pushing Performance
Since 1945

Han PP Signal 10-pole plug metal 7-11mm




Image is for illustration purposes only. Please refer to product description.

Part number	09 35 262 0401
Specification	Han PP Signal 10-pole plug metal 7-11mm
HARTING eCatalogue	https://b2b.harting.com/09352620401

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Signal
Element	Connector sets
Specification	AIDA compliant
Features	Intuitive locking mechanism

Version

Termination method	Crimp termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	10
Locking type	PushPull
Details	When installing a PROFINET system, observe the PROFINET installation guideline.
Pack contents	incl. metal housing and female insert

Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.1 mm
Contact spacing (termination side)	2.4 mm 3 mm
Contact spacing (mating side)	2.4 mm 3 mm



Pushing Performance
Since 1945

Technical characteristics

Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Clearance distance	≥1.1 mm
Creepage distance	≥1.1 mm
Insulation resistance	>10 ⁹ Ω
Contact resistance	≤10 mΩ
Limiting temperature	-40 ... +85 °C
Insertion force	50 N
Withdrawal force	50 N
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	7 ... 11 mm
Clamping range	7 ... 11 mm
Test voltage U _{r.m.s.}	1.5 kV (contact-contact) 1.5 kV (contact-ground)
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 10 sweep cycles acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 11 ms, 10 shocks / axis and direction

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (O-ring)	NBR
Material (cable seal)	TPE
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 61076-3-119 Mating face
	EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	10
Net weight	1 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140054486
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)