

NLV25T-068J-PF



Applications	Commercial Grade
Feature	No Directivity
	Wire Wound
	Ferrite Core
Series Type	NLV25-PF
Status	EOL announced Recommended Alternate Part No. : NLV25T-068J-EF (Interchangeability is not guaranteed.) Discontinue Issue Date : Nov.19, 2024 Last Purchase Order Date : Mar.31, 2026 Last Shipment Date : Sep.30, 2026
Brand	TDK



Size	
Length(L)	2.50mm ± 0.20 mm
Width(W)	2.00mm ± 0.10 mm
Thickness Height	1.80mm ± 0.10 mm
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.50mm Nom.
Recommended Land Pattern (C)	1.50mm Nom.

Electrical Characteristics	
Inductance	68nH $\pm 5\%$ at 100MHz
Rated Current	320mA
DC Resistance [Typ.]	
DC Resistance [Max.]	650m Ω
Self Resonant Frequency [Min.]	1.05GHz
Self Resonant Frequency [Typ.]	
Q [Min.]	20 at 100MHz
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Wave (Flow) Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

NLV25T-068J-PF



Package Quantity	2000pcs
------------------	---------





Weight	0.025g
--------	--------

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

NLV25T-068J-PF



Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.



! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

NLV25T-068J-PF



Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.