Part Number : 1202480066
Product Description : MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 8 Ports, LEDs for 2 PNP Sensors, 2 (IO) per port, with Integral M23 (19-Pole) Home Run Connector
Series Number : 120248
Status : Active
Product Category : Passive Distribution Boxes
Engineering Part Number : BTB803P-FBC



Documents and Resources

Drawings

1202480066_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120248
Description	MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 8 Ports, LEDs for 2 PNP Sensors, 2 (IO) per port, with Integral M23 (19-Pole) Home Run Connector
IP Rating	IP67, IP68
Product Name	MPIS
UPC	889056154710

Agency

UL	E152210

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	Dual-in PNP
Voltage - Maximum	10-30V DC
Wiring Configuration	Dual I/O per Port

Physical

Bus I/O	N/A
Cable Connector Orientation	N/A

Downloaded from Arrow.com.

Home Run Cable Length	N/A
Home Run Connector	M23 - 19 pole
Home Run Interface	Integrated Connector
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	N/A
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	289.000/g
Orientation	Top-Mount
Poles	5
Poles (wired)	5
Ports	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR

Downloaded from Arrow.com.