





REV.	DATE	DESCRIPTION
A	11/14/97	ADD CONTACT PIN
B	07/01/04	UPDATE DRAWING FORMAT
C	02/21/06	ADD "B1695A" TO PART DESCRIPTION / .255" HEX CRIMP



RECOMMENDED CABLE
STRIPPING DIMENSIONS



- NOTE:
1. CRIMPED FERRULE – HEX CRIMP SIZE .255"
 2. CRIMPED CONTACT PIN – HEX CRIMP SIZE .068"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						02/21/06
6						CHECKED			PART DESCRIPTION BNC CRIMP PLUG (FOR RG-6/U, B1695A PLENUM CABLE)				
5						ISSUED							
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1						
3	CONTACT PIN	BRASS	GOLD	1				PART NO. 112519					
2	INSULATOR	DELIRIN	NATURAL	1									
1	BODY	BRASS	NICKEL	1				DWG. NO. 112519.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112519.DWG						
								REV.	C	SIZE	A	SCALE	NA