

Han C axial module female 2,5-8mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 003 2701
Specification	Han C axial module female 2,5-8mm²
HARTING eCatalogue	https://b2b.harting.com/09140032701

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® C module

Version

Termination method	Axial screw termination
Gender	Female
Number of contacts	3

Technical characteristics

Conductor cross-section	2.5 ... 8 mm²
Rated current	40 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current acc. to UL	40 A
Rated voltage acc. to UL	600 V
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤0.3 mΩ
Stripping length	5 mm @ 2.5 mm²
	5 mm @ 4 mm²
	8 mm @ 6 mm²



Pushing Performance

Technical characteristics

Tightening torque	1.5 Nm @ 2.5 mm²
	1.5 Nm @ 4 mm²
	2 Nm @ 6 mm²
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 PVVA8.E318390

Commercial data

Packaging size	2
Net weight	31 g



Pushing Performance

Commercial data

Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440217 Module for industrial connectors (power/signals)