


NEW



DIMENSIONS (mm inch)



RATING

1. Standard speed

Table with 9 columns: Part number, Rated voltage (V), Input power (W), Rated current (mA), Rotation speed (r/min), Max. air flow (m³/min), Max. static pressure (Pa), Noise (dB(A)), Weight (g). Rows include ASFN10371 and ASFN10372.

2. Middle speed


Table with 9 columns: Part number, Rated voltage (V), Input power (W), Rated current (mA), Rotation speed (r/min), Max. air flow (m³/min), Max. static pressure (Pa), Noise (dB(A)), Weight (g). Rows include ASFN12371 and ASFN12372.

3. Low speed

Table with 9 columns: Part number, Rated voltage (V), Input power (W), Rated current (mA), Rotation speed (r/min), Max. air flow (m³/min), Max. static pressure (Pa), Noise (dB(A)), Weight (g). Rows include ASFN14371 and ASFN14372.

Notes: 1. Values above without designations are averages. 2. Noise levels are based on measurements taken at a distance of 1 m from the front of the fan. *1: Designates maximum values *2: Designates average values


DATA (Airflow - Static pressure Characteristic Curve)



MATERIALS USED

Frame: plastic
Propeller: plastic
Bearings: ball bearings
Lead wires: UL1007 and AWG24

WIRING DIAGRAM



SPECIFICATIONS

Table with 2 columns: Specification and Value. Rows include Ambient temperature, Ambient humidity, Temperature rise, Breakdown voltage, Insulation resistance, Vibration resistance, Lead wire tensile strength, Fan blockage, Reverse polarity power connection, and Expected life.