


COAXIAL CONNECTOR, TNC, 50 Ohm, Right angle cable plug (male)

16_TNC-50-2-7/133_N

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz

**Product configuration**

Interface type	Gender	Standard
TNC	plug	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	32 dB	1.052

Mechanical data

Weight	0.0196 kg
Mating cycles	500
Cable entry centre contact	soldered

COAXIAL CONNECTOR, TNC, 50 Ohm, Right angle cable plug (male)

16_TNC-50-2-7/133_N

Mechanical data		
Cable entry outer contact		crimped
Environmental data		
Operation temperature		-65 °C ... 165°C
Ordering Information Table		
Item number	Item description	Packaging type
23001716	16_TNC-50-2-7/133_NE	Single
Suitable cables		
Cable group		U4 - 2 mm / 50 Ohm
Suitable cables		ENVIROFLEX_316_D
		K_02252_D
		G_02232_D
Additional Information		
Remarks		El. optimized for cable K_02252_D
Only as assembly		No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2983 / Date of publication: 25.11.2023 / uncontrolled copy