


Features

- 1000 V / 1 A rating
- Tiny DFN3538 package (3.5 x 3.8 mm)
- Low profile (1.15 mm)
- High thermal dissipation
- RoHS* and Halogen Free**


Applications

- USB wall sockets
- AC/DC power supplies
- Battery chargers
- Medical equipment (low/medium risk)***
- Industrial equipment

CD-MMBL110S Surface Mount Bridge Rectifier Diode

General Information

Manufacturers of consumer electronics, portable communication, medical and industrial equipment are challenging the semiconductor industry to develop innovated packaging technologies and component miniaturization.



Bourns® CD-MMBL110S Bridge Rectifier is housed in a tiny DFN3538 package (3.5 mm x 3.8 mm x 1.15 mm), minimizing PCB real estate and fitting into designs with height constraints. Besides the benefit of a compact footprint compared to a conventional gull-wing package, its flat no-leads package construction features superior coplanarity, improved solder joints, and virtually eliminates short circuit conditions during manufacturing.

Bourns® CD-MMBL110S Bridge Rectifier is rated at 1000 V / 1 A with enhanced thermal dissipation capability[1].

Additional Information

Click these links for more information:

PRODUCT | TECHNICAL LIBRARY | INVENTORY | SAMPLES | CONTACT

Absolute Maximum Ratings (@ T_A = 25 °C Unless Otherwise Noted)

Parameter	Symbol	CD-MMBL110S	Unit
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	1000	V
Maximum Average Forward Rectified Current (T_A = 55 °C)	$I_{F(AV)}$	1	A
Peak Forward Surge Current 8.3 ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method)	I_{FSM}	30	A
Operating Temperature Range	T_J	-55 to +150	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C

Electrical Characteristics (@ T_A = 25 °C Unless Otherwise Noted)

Parameter	Symbol	CD-MMBL110S					Unit
		Test Conditions		Min.	Typ.	Max.	
Instantaneous Forward Voltage	V_F	I_F = 0.4 A			0.9	1.0	V
		I_F = 1.0 A				1.1	
Repetitive Peak Reverse Current	I_{RRM}	$V_R = V_{RRM}$	T_A = +25 °C		0.08	5.0	μA
			T_A = +125 °C			100	μA
Junction Capacitance	C_J	V_R = 4 V, f = 1.0 MHz			9		pF
Thermal Resistance, Junction to Air[1]	$R_{\Theta JA}$				130		°C / W
Thermal Resistance, Junction to Case[1]	$R_{\Theta JC}$				40		°C / W

NOTE 1: Measured when mounted on PCB with 1.3 mm x 1.3 mm (0.05 inch x 0.05 inch) copper pad areas.

WARNING Cancer and Reproductive Harm
www.P65Warnings.ca.gov


*RoHS Directive 2015/863, Mar 31, 2015 and Annex.
**Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.
***Bourns® products have not been designed for and are not intended for use in "lifesaving," "life-critical" or "life-sustaining" applications nor any other applications where failure or malfunction of the Bourns® product may result in personal injury or death. See Legal Disclaimer Notice www.bourns.com/docs/legal/disclaimer.pdf

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.


Downloaded from Arrow.com.

Rating and Characteristic Curves


Forward Current Derating Curve




Maximum Non-Repetitive Peak Forward Surge Current




Forward Characteristics



Reverse Characteristics



Typical Junction Capacitance



Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.
The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at
www.bourns.com/docs/legal/disclaimer.pdf.


Downloaded from Arrow.com.

CD-MMBL110S Surface Mount Bridge Rectifier Diode


BOURNS®

Product Dimensions


Package: DFN3538



Typical Part Marking



Recommended Footprint



How to Order

CD - MMBL1 10 S - H

Common Code
Chip Diode

Model
MMBL = MMBL Bridge Series

Average Forward Current
1 = 1 A

Reverse Voltage
10 = 1000 V

Forward Voltage Suffix
S = Standard Forward Voltage


Reel
(blank) = 13-inch Reel
-H = 7-inch Reel


Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.
The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

Packaging Information

The surface mount product is packaged in a 12 mm x 8 mm tape and reel format per EIA-481 standard.





DIMENSIONS: MM / (INCHES)

Item	Symbol	CD-MMBL110S	CD-MMBL110S-H
Carrier Width	A	5.90 ± 0.10 (0.232 ± 0.004)	3.78 ± 0.10 (0.149 ± 0.004)
Carrier Length	B	6.50 ± 0.10 (0.256 ± 0.004)	4.16 ± 0.10 (0.164 ± 0.004)
Carrier Depth	C	1.50 ± 0.10 (0.059 ± 0.004)	1.52 ± 0.10 (0.060 ± 0.004)
Sprocket Hole	d	1.55 ± 0.05 (0.061 ± 0.002)	1.55 ± 0.05 (0.061 ± 0.002)
Reel Outside Diameter	D	330 (12.992)	178 ± 2.0 (7.008 ± 0.079)
Reel Inner Diameter	D_1	50.0 (1.969) MIN.	50.0 (1.969) MIN.
Feed Hole Diameter	D_2	13.0 ± 0.20 (0.512 ± 0.008)	13.0 ± 0.5 (0.512 ± 0.020)
Sprocket Hole Position	E	1.75 ± 0.10 (0.069 ± 0.004)	1.75 ± 0.10 (0.069 ± 0.004)
Punch Hole Position	F	5.50 ± 0.05 (0.217 ± 0.002)	5.50 ± 0.05 (0.217 ± 0.002)
Punch Hole Pitch	P	8.00 ± 0.10 (0.315 ± 0.004)	8.00 ± 0.10 (0.315 ± 0.004)
Sprocket Hole Pitch	P_0	4.00 ± 0.10 (0.157 ± 0.004)	4.00 ± 0.10 (0.157 ± 0.004)
Embossment Center	P_1	2.00 ± 0.05 (0.079 ± 0.002)	2.00 ± 0.05 (0.079 ± 0.002)
Overall Tape Thickness	T	0.20 ± 0.10 (0.008 ± 0.004)	0.23 ± 0.10 (0.009 ± 0.004)
Tape Width	W	12.00 ± 0.20 (0.472 ± 0.008)	12.0 ± 0.30 (0.472 ± 0.012)
Reel Width	W_1	18.7 (0.736) MAX.	18.7 (0.736) MAX.
Quantity per Reel	--	5,000	1,400

BOURNS®

Asia-Pacific:
Tel: +886-2 2562-4117
Email: asiacus@bourns.com

Europe:
Tel: +36 88 885 877
Email: eurocus@bourns.com

The Americas:
Tel: +1-951 781-5500
Email: americus@bourns.com

www.bourns.com

10/21

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Downloaded from Arrow.com.

Legal Disclaimer Notice

BOURNS®

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."

- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automate Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.

- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.

- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: https://www.bourns.com/legal/disclaimers-terms-and-policies
PDF: https://www.bourns.com/docs/Legal/disclaimer.pdf

Downloaded from Arrow.com.