



Color: white

Locking system WINSTA® MINI

When using the locking system from the WINSTA® MINI product line, error-free installation is guaranteed. You can rely on the quality of WINSTA® components from WAGO for your electrical installation accessories too. WINSTA® MINI satisfies the demand for miniaturisation. Our smallest pluggable connection system is primarily suited for lights, for instance, since due to LED technology, these offer less and less space for the connection technology.

Push-in CAGE CLAMP® spring pressure connection technology – pluggable installation instead of laborious screw connections!

WINSTA® is the pluggable connection system that is perfectly tailored to the strict requirements of electrical installation. It ensures fast, secure and, above all, error-free installation of components and cables. Now you can also cut installation costs without compromising safety and quality: with protection against mismatching reduces the need for servicing and prevents unnecessary downtime.

- consistent IP40 protection
- rapid, structured electrical installation

Connection data

Connection 1

Actuation type Finger-operated lever

Physical data

| | |
|--------|-------------------------|
| Width | 9 mm / 0.354 inches |
| Height | 6.73 mm / 0.265 inches |
| Depth | 26.23 mm / 1.033 inches |

Mechanical data

Suitable for flying leads; manually operated

Material data

| | |
|------------------------------------|--|
| Note (material data) | Information on material specifications can be found here |
| Color | white |
| Insulation material (main housing) | Polyamide (PA66) |
| Flammability class per UL94 | V0 |
| Fire load | 0.018 MJ |
| Weight | 0.6 g |

Environmental requirements

| | |
|--|--|
| Processing temperature | -5 ... +40 °C |
| Continuous operating temperature | -35 ... +85 °C |
| Note on continuous operating temperature | Insulating parts for temperatures ≤ 105 °C |

Commercial data

| | |
|-----------------------|---------------|
| PU (SPU) | 100 (50) pcs |
| Packaging type | Box |
| Country of origin | DE |
| GTIN | 4055143356923 |
| Customs tariff number | 85389099990 |

Product classification

| | |
|-------------|----------------------|
| UNSPSC | 39121702 |
| eCl@ss 10.0 | 27-44-06-92 |
| eCl@ss 9.0 | 27-44-06-92 |
| ETIM 9.0 | EC002863 |
| ETIM 8.0 | EC002863 |
| ECCN | NO US CLASSIFICATION |

Environmental Product Compliance

| | |
|------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |
|------------------------|-------------------------|

Approvals / Certificates

Approvals for marine applications



| Approval | Standard | Certificate Name |
|-----------------------|----------|------------------|
| LR Lloyds Register | EN 61535 | 08/20047 (E2) |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 890-121



Documentation

Bid Text

890-121 13.04.2017 doc 21.50 KB



890-121 19.02.2019 xml 2.62 KB



CAD/CAE-Data

CAD data

2D/3D Models 890-121



CAE data

ZUKEN Portal 890-121

