



Search by part # or keyword

Products

Industries &
Solutions

Resources

TE Store

Sign In



Application Tooling > Portable Crimp Tools

91522-1

CERTICRIMP 2,SAHT MINI UMNL



AMP

TE Internal #: **91522-1**

TE Internal Description: **CERTICRIMP 2,SAHT MINI UMNL**

Tool Grade : **Premium Crimp Tooling**

Ratchet Configuration : **Not Releasable, Not Adjustable**

Die Sets Type : **Fixed In Tool**

Specification Type : **TE Product Specification (114-)**

Certification : **Yes – Certificate Included**

Similar Products

 |

Digital Datasheet

Compatible Parts & Tooling

Free Shipping to select countries.
Exclusions apply. See complete details at [TE Store FAQs](#)

QTY:

Extended Price:

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Datasheets &
Catalog Pages

AMP Circular Connectors for Commercial Signal &
Power Applications Continued

[ENG_CS_82021_CPC_sections6-9_0707.pdf](#)

English

[ENG_CS_1-1773864-7_0915.pdf](#) English

[ENG_DS_1583000_D6.pdf](#) English

[ENG_DS_1-1773458-0_MINI_UNIVERSAL_MNL_1011.pdf](#) English

[ENG_DS_1-1773838-7_0718.pdf](#) English

[ENG_DS_1-1773953-1_0618.pdf](#) English

Product
Specifications

Crimping of Mini-Universal MATE-N-LOK Contact

[JPN_SS_114-5050_H.tif](#) Japanese

Application Specification

[JPN_SS_114-5050_H.pdf](#) Japanese

Instruction Sheets

Instruction Sheet (U.S.)

[ENG_SS_408-8547_L_408-8547.pdf](#) English

Instruction Sheet (non U.S.)

[JPN_SS_408-8547-1_B.pdf](#) Japanese

Please review product documents or [contact us](#) for the latest agency approval information.

Feedback



Other

Tool Grade : **Premium Crimp Tooling**
Ratchet Configuration : **Not Releasable, Not Adjustable**
Die Sets Type : **Fixed In Tool**
Specification Type : **TE Product Specification (114-)**
Certification : **Yes – Certificate Included**
Power Type : **Battery, Electric, Manual**
Tool Type : **CERTI-CRIMP II, Straight Action Hand Tool**
Crimp Form-Wire Barrel Type : **Open Barrel - F Crimp**

EU RoHS
Directive
2011/65/EU

This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).

EU ELV Directive
2000/53/EC

China RoHS 2
Directive MIIT
Order No 32, 2016

EU REACH
Regulation (EC)
No. 1907/2006

Current ECHA Candidate List: **JUL 2019 (201)**
Candidate List Declared Against: **JUL 2017 (174)**

Halogen Content

Solder Process
Capability

Not applicable for solder process capability

Statement of
Compliance

[Statement of Compliance](#) pdf

Compliance
Documents

There may be Environmental Compliance related documents on the [DOCUMENTATION Tab](#)

Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU.





the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?

<div>PORTABLE CRIMP TOOLS</div> <div>91522-1</div> <div>CERTICRIMP 2, SAHT MINI UMNL</div> <div></div> <div>From<div>In-Stock</div></div> <div>Tool Grade : Premium Crimp Tooling Ratchet Configuration : Not Releasable, Not Adjustable Die Sets Type : Fixed In Tool Specification Type : TE Product Specification (114-) ...</div>	<div>PORTABLE CRIMP TOOLS</div> <div>91596-1</div> <div>SDE SAHT 20-16 DYNAMIC D5-SS</div> <div></div> <div>From<div>In-Stock</div></div> <div>Tool Grade : Premium Crimp Tooling Ratchet Configuration : Not Releasable, Not Adjustable Die Sets Type : Fixed In Tool Specification Type : TE Product Specification (114-) ...</div>	<div>PORTABLE CRIMP TOOLS</div> <div>91500-4</div> <div>CCII SDE SAHT-SMALL WIRE INS</div> <div></div> <div>From<div>In-Stock</div></div> <div>Tool Grade : Premium Crimp Tooling Ratchet Configuration : Not Releasable, Not Adjustable Die Sets Type : Fixed In Tool Specification Type : TE Product Specification (114-) ...</div>	<div>PORTABLE CRIMP TOOLS</div> <div>91500-1</div> <div>CERTICRIMP 2, SAHT UMN20-14</div> <div></div> <div>From<div>In-Stock</div></div> <div>Tool Grade : Premium Crimp Tooling Ratchet Configuration : Not Releasable, Not Adjustable Die Sets Type : Fixed In Tool Specification Type : TE Product Specification (114-) ...</div>
--	--	---	---

