Medium Power Silicon Rectifier Diodes, (Stud Version), 12 A



DO-4 (DO-203AA)

FEATURES

- Voltage ratings from 50 V to 1000 V
- High surge capability
- Low thermal impedance
- High temperature rating
- Can be supplied as JAN and JAN-TX devices in accordance with MIL-S-19500/260
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS COMPLIANT

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	12 A
Package	DO-4 (DO-203AA)
Circuit configuration	Single

MAJOR RATINGS AND CHARACTERISTICS			
PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{F(AV)}$		**12**	A
	T_C	**150**	°C
I_{FSM}	50 Hz	230	A
	60 Hz	**240**	
I^2t	50 Hz	260	A^2s
	60 Hz	240	
T_J		-65 to +200	°C
V_{RRM}	Range	**50 to 1000**	V

Note

- JEDEC® registered values are in bold

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	V_{RRM}, MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE (T_C = -65 °C TO 200 °C) V	$V_{R(RMS)}$, MAXIMUM RMS REVERSE VOLTAGE (T_C = -65 °C TO 200 °C) V	V_{RSM}, MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE (T_C = -65 °C TO 200 °C) V	V_{RM}, MAXIMUM DIRECT REVERSE VOLTAGE (T_C = -65 °C TO 200 °C) V
VS-1N1199A	**50**	**35**	**100**	**50**
VS-1N1200A	**100**	**70**	**200**	**100**
VS-1N1201A	**150**	**105**	**300**	**150**
VS-1N1202A	**200**	**140**	**350**	**200**
VS-1N1203A	**300**	**210**	**450**	**300**
VS-1N1204A	**400**	**280**	**600**	**400**
VS-1N1205A	**500**	**350**	**700**	**500**
VS-1N1206A	**600**	**420**	**800**	**600**
VS-1N3670A	**700**	490	**900**	**700**
VS-1N3671A	**800**	560	**1000**	**800**
VS-1N3672A	**900**	630	**1100**	**900**
VS-1N3673A	**1000**	700	**1200**	**1000**
VS-1N3624	**1000**	1200	**1400**	**1000**

Notes

- JEDEC® registered values are in bold
- Basic part number indicates cathode to case; for anode to case, add “R” to part number, e.g., 1N1199**R**A

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

FORWARD CONDUCTION					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current at case temperature	$I_{F(AV)}$	180° sinusoidal conduction		**12**	A
				150	°C
Maximum peak one cycle non-repetitive surge current	I_{FSM}	Half cycle 50 Hz sine wave or 6 ms rectangular pulse	Following any rated load condition and with rated V_{RRM} applied	230	A
		Half cycle 60 Hz sine wave or 5 ms rectangular pulse		**240**	
		Half cycle 50 Hz sine wave or 6 ms rectangular pulse	Following any rated load condition and with V_{RRM} applied following surge = 0 V	275	
		Half cycle 60 Hz sine wave or 5 ms rectangular pulse		285	
Maximum I^2t for fusing	I^2t	t = 10 ms	With rated V_{RRM} applied following surge, initial T_J = 200 °C	260	A^2s
		t = 8.3 ms		240	
Maximum I^2t for individual device fusing		t = 10 ms	With V_{RRM} = 0 V following surge, initial T_J = 200 °C	370	
		t = 8.3 ms		340	
Maximum $I^2\sqrt{t}$ for individual device fusing	$I^2\sqrt{t}$ (1)	t = 0.1 ms to 10 ms, V_{RRM} = 0 V following surge		3715	$A^2\sqrt{s}$
Maximum forward voltage drop	V_{FM}	$I_{F(AV)}$ = 12 A (38 A peak), T_C = 25 °C		**1.35**	V
Maximum average reverse current	V_{RRM} = 50 V	$I_{R(AV)}$ (2)	Maximum rated $I_{F(AV)}$ and T_C	**3.0**	mA
	V_{RRM} = 100 V			**2.5**	
	V_{RRM} = 150 V			**2.25**	
	V_{RRM} = 200 V			**2.0**	
	V_{RRM} = 300 V			**1.75**	
	V_{RRM} = 400 V			**1.5**	
	V_{RRM} = 500 V			**1.25**	
	V_{RRM} = 600 V			**1.0**	
	V_{RRM} = 700 V			**0.9**	
	V_{RRM} = 800 V			**0.8**	
	V_{RRM} = 900 V			**0.7**	
	V_{RRM} = 1000 V			**0.6**	

Notes

- JEDEC® registered values are in bold

(1) I^2t for time $t_x = I^2\sqrt{t} \times \sqrt{t_x}$

(2) Maximum peak reverse current (I_{RM}) under same conditions ≈ 2 x rated $I_{R(AV)}$

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum operating case and storage temperature range		T_C, T_{Stg}		**-65 to 200**	°C
Maximum internal thermal resistance, junction to case		R_{thJC}	DC operation	**2.0**	°C/W
Thermal resistance, case to sink		R_{thCS}	Mounting surface, smooth, flat and greased	0.5	
Mounting torque	minimum		Torque applied to nut; non-lubricated threads	1.36 (12)	N · m (lbf · in)
	maximum			1.69 (15)	
	minimum		Torque applied to nut; lubricated threads	1.07 (9.45)	
	maximum			1.30 (11.55)	
	minimum		Torque applied to device case; lubricated threads	1.17 (10.35)	
	maximum			1.43 (12.65)	
Approximate weight				7.0	g
				0.25	oz.
Case style			JEDEC®	DO-4 (DO-203AA)	

Note

- JEDEC registered values are in bold

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.




Fig. 1 - Average Forward Current vs.
Maximum Allowable Case Temperature




Fig. 2 - Maximum Low Level Forward Power Loss vs.
Average Forward Current




Fig. 3 - Maximum High Level Forward Power Loss vs.
Average Forward Current




Fig. 4 - Maximum Forward Voltage vs. Forward Current




Fig. 5 - Maximum Transient Thermal Impedance,
Junction to Case vs. Pulse Duration




Fig. 6 - Maximum Non-Repetitive 50 Hz Surge Current vs.
Number of Current Pulses


LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95311

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

DO-203AA (DO-4)

DIMENSIONS in millimeters (inches)



Downloaded from Arrow.com.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2026 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.