


1376383-5 Product Details

Share

Print

Email



5mm Power Key Connectors

5mm B-T-W Conn. 3P HDR ASSEMBLY (GWT)

1376383-5

TE Internal Number: 1376383-5

Active

View 3D PDF

Product Highlights

View All

- 5.0 Power Key Connectors Product Line
- Wire-to-Board
- Connector
- Glow Wire Rating = Glow Wire
- Header

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Please Note:

Use the Product Drawing For all design activity

Product Type Features

Product Line	5.0 Power Key Connectors
Product Type	Connector
Connector Type	Header
PCB Mount Retention	With
PCB Mount Alignment	Without
PCB Mount Retention Type	Mounting Post/Kinked Legs
PCB Mounting Orientation	Vertical
Sealed	No
Shape	Rectangular
CSA File Number	LR7189

Mechanical Attachment

Mating Retention Type	Latch(ing)
-----------------------	------------

Electrical Characteristics

Contact - Rated Current (A)	9
Hot Pluggable	No
Operating Voltage Reference	AC
Operating Voltage (VAC)	300
UL Voltage Rating (VAC)	300

Termination Features

Termination Method to PC Board	Through Hole - Press Fit
--------------------------------	--------------------------

Dimensions

Mating Post Length (mm [in])	6.30 [0.248]
Tail Length (mm [in])	3.5 [0.138]
PCB Thickness, Recommended (mm [in])	1.60 [0.063]
Length (X-Axis) (mm [in])	16.60 [0.653]
Width (Z-Axis) (mm [in])	14.10 [0.555]
Profile Height (Y-Axis) (mm [in])	7.00 [0.275]

Body Features

Mating Retention	With
Header Type	Shrouded
Selectively Loaded	No

Contact Features

Contact Type	Pin
Contact Base Material	Copper Alloy
Contact Plating, Mating Area, Material	Tin
Contact Design	Tab
Contact Plating, Mating Area, Thickness (µm [µin])	0.8 [31.49]
Contact Plating, Termination Area, Material	Tin
Contact Plating, Termination Area, Thickness (µm [µin])	1 [39.37]

Housing Features

Connector Style	Receptacle
Housing Color	Natural
Mating Alignment	Without
Centerline (mm [in])	5.00 [0.197]
Housing Material	Nylon 6/6 GF

Configuration Features

Number of Positions	3
Number of Rows	1
Tail Orientation	In-line
Shrouded	Yes

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
Agency/Standard	UL, CSA
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0

Identification Marking

Keying	A
--------	---

Environmental

Operating Temperature (°C [°F])	-30 - +105 [-22 - +221]
---------------------------------	-------------------------

Conditions for Usage

Glow Wire Rating	Glow Wire
Applies To	Printed Circuit Board

Operation/Application

Application Use	Wire-to-Board
Contact Transmits (Typical Application)	Signal (Data)/Power

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

Brand	AMP
-------	-----

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling