






PCB Layout

| POLE | 1      | 2      | 3      | 4      | 5      | 6      | 7      | 8      | 9      | 10     | 11     | 12     | 13     | 14     | 15    | 16     |
|------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|--------|
| A    |        | 13.70  | 20.05  | 26.40  | 32.75  | 39.10  | 45.45  | 51.80  | 58.15  | 64.50  | 70.85  | 77.20  | 83.55  | 89.90  | 96.25 | 102.60 |
| B    |        | 6.35   | 12.70  | 19.05  | 25.40  | 31.75  | 38.10  | 44.45  | 50.80  | 57.15  | 63.50  | 69.85  | 76.20  | 82.55  | 88.90 | 95.25  |
| POLE | 17     | 18     | 19     | 20     | 21     | 22     | 23     | 24     | 25     | 26     | 27     | 28     | 29     | 30     |       |        |
| A    | 108.95 | 115.30 | 121.65 | 128.00 | 134.35 | 140.75 | 147.40 | 153.40 | 159.75 | 166.10 | 172.45 | 178.80 | 185.15 | 191.50 |       |        |
| B    | 101.60 | 107.95 | 114.30 | 120.65 | 127.00 | 133.35 | 139.70 | 146.05 | 152.40 | 158.75 | 165.10 | 171.45 | 177.80 | 184.15 |       |        |

| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
|                                                |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

### SPECIFICATIONS

|                        |                               |
|------------------------|-------------------------------|
| VOLTAGE & CURRENT:     | 250V, 10A                     |
| WITHSTANDING VOLTAGE:  | AC 2000 V/Min                 |
| INSULATION RESISTANCE: | 1000 MΩ OR MORE AT DC 500 V   |
| TEMPERATURE RANGE:     | -40 °C ~ +105 °C              |
| SCREW TORQUE VALUE:    | 6.1 Lb-In.                    |
| WIRE RANGE:            | 22 - 18 AWG                   |
| 1) MOLDED PARTS:       | POLYIMIDE 66, UL 94 V-0 BLACK |
| 2) TERMINAL:           | BRASS, 0.8t, Tin PLATED       |
| 3) TERMINAL SCREWS:    | STEEL, Ni PLATED, M3          |

APPROVAL: 

RoHS Compliant

PART NUMBER:

OSTYK211XX030

No. of Poles

02: 2 Poles  
03: 3 Poles  
04: 4 Poles

...

30: 30 Poles

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



| TITLE                 |                      | OSTYK-211 Series     |                      |                                                                                       |                                               |
|-----------------------|----------------------|----------------------|----------------------|---------------------------------------------------------------------------------------|-----------------------------------------------|
| PART NO.              | OSTYK211XX030        |                      |                      | DWG NO.                                                                               | OSTYK211XX030.DWG                             |
| APPROVED              | CHECKED              | DESIGNED             | DRAWN                | CUST NO.                                                                              |                                               |
| Shi Jun<br>2006.10.26 | Seamus<br>2006.10.25 | Steady<br>2006.10.20 | Steady<br>2006.10.20 |  | UNIT: mm<br>SCALE: NONE<br>SHEET: 01/01       |
|                       |                      |                      |                      | Tolerance                                                                             | X. ±0.50<br>X.X ±0.30<br>X.XX ±0.10<br>X° ±1° |
|                       |                      |                      |                      | REV:                                                                                  | D                                             |