




JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
10ESB	10.0	.040	.048	0.60	10,000	C-2V
12ESB	12.0	.040	.088	1.11	7,500	C-2F
24ESB	24.0	.040	.120	1.51	8,000	C-2F
28ESB	28.0	.040	.287	3.61	6,000	C-2F
48ESB	48.0	.040	.358	4.50	5,000	CC-2F

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DELETE CANCELLED PART NO. 6ESB	7/22/05
	RELEASED	8/16/00

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
DRAWN BY L. WENGSTROM APPV'D BY J.K. DATE 7/22/05		TITLE		T-2 TELEPHONE SLIDE BASE ANSI #5-23mol			
		SIZE	FSCM NO.	DRAWING NO.			
		A	55335	SLIDE BASE ANSI #5-23mol			
		SCALE			RELEASED DATE	REVISION DATE	REV. NO.
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		NONE		8/16/00	7/22/05	A	1 OF 1