




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL CREATED	15MAY2022	CL	WH
	A1		10JUN2022	CL	WH




SCALE 4:1



PART NUMBER	2081408-1
-------------	-----------

NOTES:

- NOTE:
1. MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 2. MATERIAL CHARACTERIES:
 3. PRODUCT RATING:
 - TEMPERATURE: -55°C TO +125°C
 - VOLTAGE: 175V(RMS)
 - CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
 - FREQUENCY RANGE: DC TO 67GHz
 4. SMPM INTERFACE MEET IEC61169-60

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Cedar Liu07MAY2022		TE Connectivity			
		CHK Cedar Liu07MAY2022					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±-		NAME SMPM RECEPTACLE,UP TO 67GHz 500HM -			
				APVD Wenke He-		PRODUCT SPEC -	
				APPLICATION SPEC -		SIZE A3	
MATERIAL TBD -				FINISH - finish_spec_2		CAGE CODE 00779	
CUSTOMER DRAWING				DRAWING NO C-2081408		RESTRICTED TO -	
				SCALE 2:1		SHEET 1 OF 1	
				REV A1			