



CATALOG LISTING
ML-1376
PAGE 1 OF 1
RELEASE NO. PR-24297
ISSUE 1
REVISIONS
CHECK
11 NOV 99
S A V
CHECK
11 NOV 99
G J W
DRAWN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	
OPERATING FORCE	3 ± 1 LBS
FULL OVERTRAVEL FORCE	7 LBS MAX
RELEASE FORCE	.5 LBS MIN
PRETRAVEL	.040 MAX
DIFFERENTIAL TRAVEL	.020 MAX
OVERTRAVEL	.125 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT		
3X SPDT		
LOAD	28VDC	
	SEA LEVEL	50,000 FEET
RES	1	1
IND	.5	.5
MOTOR		

THIRD ANGLE PROJECTION

SCALE 1.5 : 1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0)	±.030
TWO PLACE (.00)	±.015
THREE PLACE (.000)	±.005
ANGLES	±
WEIGHT	

- NOTES
- 1 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 2 - CORROSION RESISTANT STEEL ENCLOSURE, PLUNGER AND ROLLER
 - 3 - SWITCH SEALED PER MIL - PRF - 8805 SYMBOL 3
 - 4 - BASIC SWITCHES HAVE SOLID GOLD CONTACTS
 - 5 - SWITCH CURRENT LEVELS SHALL NOT BE MORE THAN 100 MILLIAMPS @ 28 VDC
 - 6 - PRINT CIRCUIT DAGRAM, CATALOG LISTING, DATE CODE AND NAVAIR PART NUMBER 1534AS392-2 ON NAMEPLATE
 - 7 - PLASTIC MATERIALS SHALL CONFORM TO MIL - M - 14 OR MIL - M - 24519
 - 8 - 10X MIL - W - 22759/ 11-22-9 WIRE LEADS MARKED WITH CIRCUIT IDENTIFICATION AND WIRE GAGE PER MIL - W - 5088