


**Part Number :** [348570506](#)  
**Series Number :** 34857  
**Status :** Active - Proprietary  
**Product Category :** PCB Headers and Receptacles



---

## Drawings

[348570506 sd.pdf](#)


[PK-31301-768-001.pdf](#)

[348570506 stp.zip](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active - Proprietary
Category	PCB Headers and Receptacles
Series	34857
Description	HSAutoLink II Right-Angle Sealed Header, 12 Circuits
Application	Automotive, Signal, Wire-to-Board
Comments	Higher current capability depending of the connector loading, please contact Molex for further technical details. 36 V max (Power lines) / 60 V max (Differential pair ,Äi Wire/shield or Wire/Wire).
Component Type	PCB Header
Product Name	HSAutoLink II
UPC	884982730991

### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	36V

### Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes

Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.498/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.406µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

This document was generated on Apr 15, 2026