



MODEL NUMBER	IMPEDANCE OHMS
BJ23	50
JDJ23	75

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR REPRODUCED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.


REVISIONS			
REV	DESCRIPTIONS	DATE	APPROVED
C	REVISED PER ECO # 6674	8-4-08	Q. Jones



SCALE 3/1



SCALE 2/1



RECOMMENDED
PANEL CUT-OUT
SCALE 3/1

RED INDICATES ORIGINAL

- MAXIMUM PANEL THICKNESS: .147
- FINISH: TFS-1A (NICKEL)
- 50/75 OHM COAXIAL REAR MOUNT
NON-INSULATED 2-LUG BNC TYPE
SOLDER POT BULKHEAD RECEPTACLE

NOTES: UNLESS OTHERWISE SPECIFIED.

TROMPETER 25MM 40 TER MIL-STD-22 DIMENSIONS ARE IN INCHES AND DECIMALS THEREOF UNLESS OTHERWISE SPECIFIED		TOL: UNLESS SPECIFIED: XX = .07 .XX = .010 ANGLE = 1°		TROMPETER RF connectivity a cinch connectivity solutions brand	
J. CARPENTER CHG 7-31-08 QUANTITY PARTS APPROVED 7/31/08 PROJECT NO. 105-1402	MATERIAL: FINISH:	TITLE: U/BJ23		SIZE RANGE CODE A 14949	
NEXT ASSY 105-1402		DO NOT SCALE DIMS SCALE 3/1		DATE 3-12-02 SHEET 1C	