


C016 30G006 100 12



Data Overview

Description: Female Receptacle; Flange; 6+PE; Silver; IP67



Diese Website verwendet Cookies.

Wir verwenden Cookies, um Ihnen einen optimalen Service beim Besuch unserer Website zu ermöglichen und darüber hinaus unsere Leistungsangebote an Ihre Bedürfnisse anzupassen. Diese Cookies werden für technische und statistische Zwecke sowie für Marketing-Zwecke verwendet. Entscheiden Sie bitte selbst, welche Arten von Cookies bei der Nutzung unserer Website gesetzt werden sollen. Die Arten von Cookies, die wir einsetzen, sind nachfolgend unter "Details" beschrieben. Weitere Informationen erhalten Sie in unserer Datenschutzerklärung.

[Impressum](#) - [Datenschutz](#)

- Anpassen
- Ablehnen
- Alles akzeptieren

Powered by Usercentrics Consent Management

50

Add to Cart

Stock of our Distributors ▾

Technical Data

General Characteristics	+
Electrical Characteristics	+
Further Characteristics	+
Downloads	+

Frequently Asked Questions

Which components belong to a complete parts list?	+
What information is available for use as a plug-in device?	+
What options are there for direct transfer to a printed circuit board?	+
How does the transmission of the cable shielding work with eco mate m?	+
Tarnishing of silver-plated contacts - what's behind it?	+
What options are there for mechanical coding?	+
How does the assembly with screw contacts work?	+
How can cable diameters between four and six millimeters be sealed?	+
How does the internal cable clamp work?	+
Are the housings UV-resistant?	+

This might interest you

Accessory »

Housing »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

- Contact
- Downloads
- Imprint
- General Conditions
- Career
- Privacy Policy
- Privacy Settings



Newsletter

E-Mail

☐ I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following [consent](#).

Subscribe to Newsletter