

# NTTFS3A08PZ

## Power MOSFET

### -20 V, -15 A, Single P-Channel, $\mu$ 8FL

#### Features

- Ultra Low  $R_{DS(on)}$  to Minimize Conduction Losses
- $\mu$ 8FL 3.3 x 3.3 x 0.8 mm for Space Saving and Excellent Thermal Conduction
- ESD Protection Level of 5 kV per JESD22-A114
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### Applications

- Battery Switch
- High Side Load Switch
- Optimized for Power Management Applications for Portable Products such as Media Tablets, Ultrabook PCs and Cellphones

**MAXIMUM RATINGS** ( $T_J = 25^\circ\text{C}$  unless otherwise stated)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	$V_{DSS}$	-20	V
Gate-to-Source Voltage	$V_{GS}$	$\pm 8$	V
Continuous Drain Current $R_{\theta JA}$ (Note 1)	$I_D$	-15	A
		-11	
Power Dissipation $R_{\theta JA}$ (Note 1)	$P_D$	2.3	W
Continuous Drain Current $R_{\theta JA} \leq 10$ s (Note 1)	$I_D$	-22	A
		-16	
Power Dissipation $R_{\theta JA} \leq 10$ s (Note 1)	$P_D$	4.9	W
Continuous Drain Current $R_{\theta JA}$ (Note 2)	$I_D$	-9	A
		-7	
Power Dissipation $R_{\theta JA}$ (Note 2)	$P_D$	0.84	W
Pulsed Drain Current	$I_{DM}$	-46	A
Operating Junction and Storage Temperature	$T_J, T_{stg}$	-55 to +150	$^\circ\text{C}$
ESD (HBM, JESD22-A114)	$V_{ESD}$	5000	V
Source Current (Body Diode)	$I_S$	-3	A
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)	$T_L$	260	$^\circ\text{C}$

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
2. Surface-mounted on FR4 board using the minimum recommended pad size.




**ON Semiconductor®**


<http://onsemi.com>

$V_{(BR)DSS}$	$R_{DS(on)}$ MAX	$I_D$ MAX
-20 V	6.7 m $\Omega$ @ -4.5 V	
	9.0 m $\Omega$ @ -2.5 V	-15 A

#### P-Channel MOSFET



#### MARKING DIAGRAM



3A08 = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
■ = Pb-Free Package

(Note: Microdot may be in either location)

#### ORDERING INFORMATION

Device	Package	Shipping <sup>†</sup>
NTTFS3A08PZTAG	WDFN8 (Pb-Free)	1500 / Tape & Reel
NTTFS3A08PZTWG	WDFN8 (Pb-Free)	5000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

# NTTFS3A08PZ

## THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Ambient – Steady State (Note 3)	$R_{\theta JA}$	55	$^{\circ}\text{C}/\text{W}$
Junction-to-Ambient – Steady State (Note 4)	$R_{\theta JA}$	148	
Junction-to-Ambient – ( $t \leq 10$ s) (Note 3)	$R_{\theta JA}$	26	

3. Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.  
 4. Surface-mounted on FR4 board using the minimum recommended pad size (40 mm<sup>2</sup>, 1 oz. Cu).

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

### OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}$ , $I_D = 250 \mu\text{A}$	-20			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(\text{BR})\text{DSS}/T_J}$			6		$\text{mV}/^{\circ}\text{C}$
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}$ , $V_{\text{DS}} = -16 \text{ V}$	$T_J = 25^{\circ}\text{C}$		-1	$\mu\text{A}$
Gate-to-Source Leakage Current	$I_{\text{GSS}}$	$V_{\text{DS}} = 0 \text{ V}$ , $V_{\text{GS}} = \pm 5 \text{ V}$			$\pm 5$	$\mu\text{A}$

### ON CHARACTERISTICS (Note 5)

Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}$ , $I_D = -250 \mu\text{A}$	-0.4		-1.0	V	
Negative Threshold Temperature Coefficient	$V_{\text{GS}(\text{TH})/T_J}$			3.3		$\text{mV}/^{\circ}\text{C}$	
Drain-to-Source On Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = -4.5 \text{ V}$	$I_D = -12 \text{ A}$		4.9	6.7	$\text{m}\Omega$
		$V_{\text{GS}} = -2.5 \text{ V}$	$I_D = -10 \text{ A}$		6.9	9.0	
Forward Transconductance	$g_{\text{FS}}$	$V_{\text{DS}} = -1.5 \text{ V}$ , $I_D = -8 \text{ A}$		62		S	

### CHARGES AND CAPACITANCES

Input Capacitance	$C_{\text{iss}}$	$V_{\text{GS}} = 0 \text{ V}$ , $f = 1.0 \text{ MHz}$ , $V_{\text{DS}} = -10 \text{ V}$		5000		pF
Output Capacitance	$C_{\text{oss}}$			600		
Reverse Transfer Capacitance	$C_{\text{rss}}$			540		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{GS}} = -4.5 \text{ V}$ , $V_{\text{DS}} = -10 \text{ V}$ , $I_D = -8 \text{ A}$		56		nC
Threshold Gate Charge	$Q_{\text{G}(\text{TH})}$			2.0		
Gate-to-Source Charge	$Q_{\text{GS}}$			6.5		
Gate-to-Drain Charge	$Q_{\text{GD}}$			15.4		

### SWITCHING CHARACTERISTICS (Note 6)

Turn-On Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{GS}} = -4.5 \text{ V}$ , $V_{\text{DS}} = -10 \text{ V}$ , $I_D = -8 \text{ A}$ , $R_G = 6.0 \Omega$		13		ns
Rise Time	$t_r$			60		
Turn-Off Delay Time	$t_{\text{d}(\text{off})}$			250		
Fall Time	$t_f$			170		

### DRAIN-SOURCE DIODE CHARACTERISTICS

Forward Diode Voltage	$V_{\text{SD}}$	$V_{\text{GS}} = 0 \text{ V}$ , $I_S = -3 \text{ A}$	$T_J = 25^{\circ}\text{C}$		-0.65	-1.0	V
Reverse Recovery Time	$t_{\text{RR}}$	$V_{\text{GS}} = 0 \text{ V}$ , $dI_S/dt = 100 \text{ A}/\mu\text{s}$ , $I_S = -6 \text{ A}$			207		ns
Charge Time	$t_a$				45		
Discharge Time	$t_b$				162		
Reverse Recovery Charge	$Q_{\text{RR}}$				234		

5. Pulse Test: pulse width = 300  $\mu\text{s}$ , duty cycle  $\leq 2\%$ .  
 6. Switching characteristics are independent of operating junction temperatures.

## TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current vs. Voltage

## TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Threshold Voltage






Figure 12. Single Pulse Maximum Power Dissipation

## TYPICAL CHARACTERISTICS



**Figure 13. Maximum Rated Forward Biased Safe Operating Area**






**Figure 14. FET Thermal Response**



SCALE 2:1

WDFN8 3.3x3.3, 0.65P  
CASE 511AB  
ISSUE D

DATE 23 APR 2012

GENERIC  
MARKING DIAGRAM\*

XXXXX = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
■ = Pb-Free Package


\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

## NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.70	0.75	0.80	0.028	0.030	0.031
A1	0.00	---	0.05	0.000	---	0.002
b	0.23	0.30	0.40	0.009	0.012	0.016
c	0.15	0.20	0.25	0.006	0.008	0.010
D	3.30	BSC		0.130	BSC	
D1	2.95	3.05	3.15	0.116	0.120	0.124
D2	1.98	2.11	2.24	0.078	0.083	0.088
E	3.30	BSC		0.130	BSC	
E1	2.95	3.05	3.15	0.116	0.120	0.124
E2	1.47	1.60	1.73	0.058	0.063	0.068
E3	0.23	0.30	0.40	0.009	0.012	0.016
e	0.65	BSC		0.026	BSC	
G	0.30	0.41	0.51	0.012	0.016	0.020
K	0.65	0.80	0.95	0.026	0.032	0.037
L	0.30	0.43	0.56	0.012	0.017	0.022
L1	0.06	0.13	0.20	0.002	0.005	0.008
M	1.40	1.50	1.60	0.055	0.059	0.063
θ	0	°	---	12	°	0
				12	°	12

## SOLDERING FOOTPRINT\*



\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON30561E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	WDFN8 3.3X3.3, 0.65P	PAGE 1 OF 1

**onsemi** and **Onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

