


Rev	AWO #	Description	Date	Appr
-		RELEASED	3/4/15	


APPROVED: _____


DATE: _____ TITLE: _____











RECOMMENDED PCB LAYOUT

SPECIFICATIONS:
Material:
Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: Brass, Nickel plated
Plating:
Gold Flash over Nickel underplate on contact area,
Tin over Copper underplate on SMT tails
Electrical:
Voltage rating: 30 VDC max.
Current rating: 1.0 Amp max.
Contact resistance: 50 mohms max.
Insulation resistance: 100 Mohms min.
Dielectric withstanding voltage: 300 VAC for 1 minute
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	3/4/15
CHECKED	NP	3/4/15
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MINI USB, TYPE B, 5 PIN, SINGLE PORT RIGHT ANGLE, SMT

SIZE	PART NO.	REV.
X	MUSB-B5-S-RA-TSMT-CS1	-

REF: S00126T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.