



Wire & Cable > Twisted Pair Cable > NEMA WC27500: Crosslinked ETFE Lightweight Cables



Operating Temperature Range: -65 – 200 °C [-85 – 392 °F]

Cable Type: MIL-DTL-27500

Operating Voltage: 600 VAC

Wire & Cable Insulation Material: Modified Radiation Cross-linked ETFE Polymer

Conductor Material: Silver-Coated Copper

[All NEMA WC27500: Crosslinked ETFE Lightweight Cables \(228\)](#)

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Wire Color (Stripe)	Blue, No Stripe
Cable Color	White
Wire Color (Base)	White
Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Silver-Coated Copper

Dimensions

Wire Size	22 AWG
-----------	--------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
Cable Type	MIL-DTL-27500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # D17660-000
D-200-82


Customers Also Bought



TE Part #3425690001
D-SCE-2.4-50-S1-4



TE Part #601154-000
D-621-0011




TE Part #814507-000
222D232-4-0



TE Part #852077-000
CTC-0039-22-9/5-93CS1963



TE Part #Y88117-8-2SV004000 PLUG ASSY	TE Part #88118-8-4P RECP ASSY	TE Part #Y52055-21-41PNV003 HERM RECP	TE Part #638627-000 TX40AB90-0804
TE Part #Y88117-8-4SV004000 PLUG ASSY	 TE Part #398665-000 TX40AB00-0804		

Documents

Product Drawings

55A1122-22-9/96-9CS2275

English

Datasheets & Catalog Pages

Raychem Wire and Cable Quick Reference Guide

English

MIL-SPEC WIRE AND CABLE

English