



D

- 1 PARTS COMPLY WITH TE SOLDERABILITY SPEC NO. 109-11-3.
- 2 CONTACT IS PLATED OVERALL WITH 0.00127[.000050] NICKEL THEN 0.000762[.000030] GOLD OVER CONTACT LENGTH INDICATED AND TIN PLATED ON SOLDER TAIL END.
- 3 DIMENSION SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.

C




B



RECOMMENDED LAYOUT FOR
1.57[.062] THICK P.C. BOARD

A

	COPPER ALLOY-PRE TIN	NYLON, NATURAL UL94V-0	350209-3
OBSOLETE	COPPER ALLOY-GOLD 2	NYLON, NATURAL UL94V-2	350209-2
	COPPER ALLOY-PRE TIN	NYLON, NATURAL UL94V-2	350209-1
	PIN MAT'L & COLOR	HSG, MAT'L & COLOR	ASS'Y NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18MAR09 RAGHAVENDRA	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK 18MAR09 SARVER MICHAEL		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2 CIRCUIT MATE-N-LOK P.C. BOARD HEADER	
	0 PLC ± -			
	1 PLC ± -			
	2 PLC ± -			
	3 PLC ± 0.38[.015]			
MATERIAL SEE TABLE	4 PLC ± -		SIZE A2	
	ANGLES ± 1°			
	FINISH			
	WEIGHT 0.000000			
	CUSTOMER DRAWING			
		APVD 18MAR09 SARVER MICHAEL	DRAWING NO C-350209	
		PRODUCT SPEC —	CAGE CODE 00779	
		APPLICATION SPEC —	SHEET 1 OF 1	
			REV S4	