

MC9S08DV16AMLC (Active)

S08DV 8-bit MCU, S08 core, 16KB Flash, 40MHz, QFP 32

[Data Sheet](#)[Product Summary](#)[Software & Tools](#)[Documentation](#)**Package :**[LQFP](#)

plastic, low profile quad; flat leaded package; 32 terminals; 0.80 mm pitch; 7 mm x 7 mm x 1.4 mm body

[Buy Options](#) | [Operating Characteristics](#) | [Environmental Information](#) | [Quality Information](#) | [Shipping Information](#)

Operating Characteristics

Parameter	Value
Flash (kB)	16
RAM (kB)	1
Core Type	S08
Operating Frequency [Max (MHz)]	20
I ² C	1

Parameter	Value
SPI	1
Supply voltage [min] (V)	2.7
Supply voltage [max] (V)	5.5
GPIO	26
Ambient Operating Temperature (Min-Max) (°C)	-40 to 85

Environmental Information

Material Declaration	PbFree	EU RoHS	Halogen Free	RHF Indicator	2nd Level Interconnect	REACH SVHC	Weight (mg)
MC9S08DV16AMLC (935317067557)	Yes	Yes Certificate Of Analysis (CoA)	Yes	D	e3	REACH SVHC	188.6

Quality Information

Material Declaration	Safe Assure Functional Safety	Moisture Sensitivity Level (MSL)	Peak Package Body Temperature (PPT) (C°)	Maximum Time at Peak Temperatures (s)
		Lead Free Soldering	Lead Free Soldering	Lead Free Soldering
MC9S08DV16AMLC (935317067557)	No	3	260	40

Shipping Information

Part Number	Harmonized Tariff (US) Disclaimer	Export Control Classification Number (US)
MC9S08DV16AMLC (935317067557)	854231	3A991A2

ABOUT NXP

[Investors](#)[Press, News, Blogs](#)

RESOURCES

[Mobile Apps](#)[Contact Us](#)

FOLLOW US



News 26 Jul 2018



NXP Semiconductors Reports Second Quarter 2018 Results

[Read More](#)

