PRODUCT DETAILS

PRODUCT DETAILS

IMSA-10112B-40Y900 （Product number (Product)： IMSA-10112B-40A-GFN1）



Document Download (Drawings can be confirmed after registration)

- Packing Specification（KS-00032.pdf）
- Product Specification（IS-101128.pdf）
- White Paper（WP_10112_JP_R1.pdf）

IMSA-10112B-40Y900 Inquire About

- Inquiries About Products
- Make a Sample Request

*Request for ordering

Products

Product number (Packaging)	IMSA-10112B-40Y900	Product number (Product)	IMSA-10112B-40A-GFN1
Category	Board to Board Connectors	Series	10112B

Specifications

Connecting Type	Plug	PCB Mounting Methods	SMT
Mating Interface	RightAngle	Connector Orientation	RightAngle
Contact Direction		Mating Direction	TopEntry
Pitch	0.5 Pitch	Solder Tail Pitch	0.5 Pitch
Pin Counts	40 Pin	Contact Plating	Gold
Plating Thickness	0.1 ㎛ Min.	Signal Spec	
Signal Transmission Speed		Length (Pitch Direction)	16.5 mm
Width (Depth)	7.2 mm	Height	6.2 mm
Rated Voltage (AC)	50 V	Rated Voltage (DC)	50 V
Rated Current	0.5 A	Withstand Voltage	250 V（AC）
Impedance Matching		Contact Resistance	100 mΩ Max.
Operating Temperature Range (Max.)	105 ℃	Operating Temperature Range (Min.)	-40 ℃
Array	Dual Row	RoHS2	Yes
Halogen Free	No	Floating	No
2-Point Contact	No	Boss Locator	Yes
Ground Terminal	No	Cap	
Tape	No	Y-Axis Floating Range	0
Y-Axis Floating Range	0	Effective Wiping Length	0.5
Amplitude		Durability	30
Card (FPC) Retention Mechanism		Packaging Type	Emboss
Package Quantity	700		

List of products in the same series

Display Option 1x4

Category	Series	Pin	Pitch(mm)	Board Mounting Method	Mating H
Board to Board Connectors	10112B	10	0.5	SMT	Right/
Board to Board Connectors	10112B	30	0.5	SMT	Right/
Board to Board Connectors	10112B	40	0.5	SMT	Right/
Board to Board Connectors	10112B	50	0.5	SMT	Right/
Board to Board Connectors	10112B	60	0.5	SMT	Right/
Board to Board Connectors	10112B	10	0.5	SMT	Right/
Board to Board Connectors	10112B	30	0.5	SMT	Right/
Board to Board Connectors	10112B	40	0.5	SMT	Right/

See More

Product Application Examples

Notes

1. Before using our website
If you consider or order our products from our website, please do so after you have confirmed and approved the terms of use (**https://www.iriso.com/en/website/**) and the following notes for using the website.

2. Notes for product descriptions
All data and other descriptions (product drawings, specifications, packaging specifications, catalogs, etc.) on this website are reference values. They may be changed without notice (including specification change, discontinuation of manufacturing, etc.). When considering or ordering any of the listed products, please contact our sales representative in advance and exchange "delivery specifications".

3. Please install protection circuits and redundant circuits on the PCB design to ensure the safety of the equipment and confirm the compatibility with our products.

4. The products described in all data categories are limited for the following recommended purposes. If you are considering the use for any purpose other than the following recommended purposes or equipment that requires reliability assurance, please contact our sales representative in advance.

5. Disclaimers
IRISO is providing all design, code, or other such information "as is" without any warranty whatsoever. By providing design, code, or other such information, IRISO makes no claim or warranty that any such implementation, alone or in combinations, is free from any potential infringement or related claims. By placing an order or making a purchase, buyer accepts full responsibility for obtaining any rights buyer may require for its implementations of any such design, code, or other such information. IRISO expressly disclaims any warranty whatsoever with respect to the adequacy of any implementation of such design, code, or other such information, including, but not limited to, any warranties or representations that any implementation is free from claims of infringement and any implied warranties, including but not limited to, warranties of merchantability or fitness for a particular purpose.

Example of inquiry

If you have a customer-specific or industry-specific quality assurance requirements for the following applications, please contact us.
* Application examples: Automotive electrical equipment, Train control system, Communication equipment (main line), Traffic signal control, Electric power, Combustion control, Fire and crime prevention equipment, Disaster prevention equipment, etc.

If you intend to use for the following specific applications, we may separately contact and verify for customer-specific quality assurance requirements.
* Specific applications: Aerospace equipment, Undersea relay equipment, Nuclear power control systems, Life-sustaining medical equipment, etc.

* Recommended applications: Computers, Office machines, Communication equipment (devices, models), Measuring equipment, AV equipment, Home appliances, FA equipment, etc.

Contact

Login

Information is automatically filled in based on your account information (you can make inquiry without log in too)

Subject Must About IMSA-10112B-40Y900

Content of Inquiry Required

Mail address Required info@example.com

Market Required
- Automotive Market
- Consumer Market
- Industrial Market

Full Name (First and Last Name) Required First name Taro Last name Iriso

Company Name Required Sample Inc.

Department Name Required Sales Department

Address Required Please select

Address2 Any 5-6-3 Marunouchi Sample Tower 101, Marunouchi, Chiyoda-ku

Position Any Please select

Occupation Any Please select

Phone Number Any 00000000 No Hyphens Required

E-mail Magazine Any To receive the latest event and technical news, please check the checkbox. If you want to unsubscribe, please uncheck the checkbox.

Privacy Policy Required

Privacy Policy

1. イリソ電子工業株式会社（以下、「当社」といいます。）は、個人情報の重要性を認識し、以下の個人情報保護方針に従い、お客様、株主の皆様及び当社従業員（以下、「お客様」といいます。）の個人情報の適切な取扱いに努力致します。当社は、個人情報の取得に関する法律（以下、「個人情報保護法」といいます。）その他の関係法

2. 上記の個人情報の取得に同意します。

I'm not a robot reCAPTCHA Privacy - Terms

Send

Copyright IRISO Electronics Co.,Ltd. All Rights Reserved.